





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2013-02-04	Lu Di	Change Rev.01 To Rev.A
B	LE31350019	2013-04-22	Lu Di	Updata The Dimensions
C	LE31460012	2014-05-26	Tony_leng	Change O-Ring



Pin Assignments
Front View



Note:

- * $\varnothing$ Important Dimension
- * Waterproof Rate: IP65(MOLDING)
- * Waterproof Rate: IP68(M12)
(Under Water 1M 24 hours)
- * Pin: Copper Alloy, Gold Plated
- * Nut: Zinc Alloy, Nickel Plated
- * Shield: Copper Alloy, Nickel Plated
- * O-Ring: Silicone, UL94V-0, Gray.
- * Jack: PBT, Black.
- * Housing: Nylon+GF, Black.
- * Panel Thickness Max: 5.0mm

UNIT:mm			TITLE			ITEM NO		DRAWN BY		DATE	
TOLERANCE			ADAPTOR, SHIELDED M12 D CODE TO RJ45			RJS-12D04FM-RS8001		Tony_leng		2014-05-26	
			SCALE	SIZE	SHEET	OF	DWG NO	CHECKED BY	DATE		
			1:1	A4	1	2	RJS-12D04FM-RS8001	Jimmy	2014-05-26		
±0.5mm			REV.	WC-REV.	QC: Inspection item	CUSTOMER		APPROVED BY		DATE	
			C	B.2		ALTW		Jo-anne		2014-05-26	

Amphenol LTW

安費諾亮泰企業股份有限公司



Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



Zipper Bag ④



* 1 Product With 1 Zipper Bag

A

UNIT:mm				TITLE ADAPTOR, SHIELDED M12 D CODE TO RJ45			Amphenol LTW 安費諾亮泰企業股份有限公司			ITEM NO RJS-12D04FM-RS8001		DRAWN BY Tony_leng		DATE 2014-05-26			
TOLERANCE ±0.5mm			SCALE 1:1							SIZE A4		SHEET 2 OF 2		DWG NO RJS-12D04FM-RS8001		CHECKED BY Jimmy	
				REV. C		WC-REV. B.2		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Jo-anne		DATE 2014-05-26			
				2		3		4		5		6		7		8	
																FMW10702-01-02A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RJS-12D04FM-RS8001](#)