





- NOTE:
- MATERIAL:
HOUSING: NYLON 6T (E630NK), UL94V-0
TERMINAL: C2700 H
 - FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1um(40u") MIN Ni OVER ALL
 - SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1517
 - THE HSG. WILL WITHSTAND EXPOSURE TO 260C
PEAK TEMP. FOR 10 SEC. IN A CONVECTION, INFRA-RED
OR VAPOR PHASE REFLOW OVEN.
 - MATING SIDE LENGTH: 2.50MM MIN.
 - PRODUCT NUMBERING:
200218 3 1 - XXX XX X X LF
- LEAD FREE
- PLATING:
1: G/F ALL OVER
4: 0.25um(10U") GOLD AT CONTACT
8: 0.76um(30U") GOLD AT CONTACT
- PACKING
T: TUBE
- PIN COUNT
04, 06, 08, ..., 48, 50
(EVERY EVEN PIN)
- STACK HEIGHT "K"
EXAMPLE: 045=4.5MM
IN 0.5MM INCREMENT



Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecn no	dr	date	linear	.X ± 0.38	projection		www.fciconnect.com	
A	T10-0088	S.LIN	10'-7-15		.XX ± 0.25				
					.XXX ± 0.15				
				angles	0° $\pm 2°$	MM		title 1.27X1.27MM BTB STACK HD VT, SMT	
				dr	STERLING LIN 10'-7-15				
				enrg	STERLING LIN 10'-7-15				
				chr	STERLING LIN 10'-7-15				
				appd	STERLING LIN 10'-7-15				
sheet index	revision sheet	A	1			scale	NA	product family 585	
								size dwg no	
								A4	
								20021831	
								code TWN	
								sheet 1 of 1	
								cage code	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

20021831-04030T4LF	20021831-05020T4LF	20021831-04036T1LF	20021831-05014T4LF	20021831-05028T4LF
20021831-04516T4LF	20021831-05050T1LF	20021831-04506T1LF	20021831-04020T4LF	20021831-04510T1LF
20021831-04006T4LF	20021831-05024T4LF	20021831-04508T1LF	20021831-04020T8LF	20021831-04012T1LF
20021831-05040T1LF	20021831-05060T1LF	20021831-04508C1LF	20021831-04520T4LF	