





SIGN	DATE	DESCRIPTION	APPROVER
△	2010.03.10	Add the 2p mark	Jacke
△	2010.03.10	Added cULus standard	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material

- Item (a) Clamp: Brass(CuZn) Ni plated
- Item (b) Terminal screw: Steel Zinc plating "-" slot type
- Item (c) Female contact: PhBz ,Tin plated
- Item (d) Terminal Cover: Thermoplastic (UL94V-0)
- Item (e) Terminal housing: Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque: 5Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

TJ xx A1x 0 xxxx G

02 2 CONTACTS
03 3 CONTACTS
... ..
16 16 CONTACTS

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

RoHS
Pb<40,000ppm

000 0 Standard @ Logo
000 A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.


Dim.A = (N-1) x 7.5+5.5
Dim.B = (N-1) x 7.5
N= number of poles

poles Dim.	2P-6P	7P-12P	13P-16P
Dim.A	±0.15	±0.30	±0.40
Dim.B	±0.15	±0.30	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	TJ-7.5mm Series						
PART NO.	TJxxA1x0xxxxG			DWG NO.	8TJ0801		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Jacke 2010.03.10	Jacke 2010.03.10		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
				SHEET: 01/01	REV.: C	X.XX	±0.10
						X°	±1°

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>TJ02A1500000G</u>	<u>TJ03A1500000G</u>	<u>TJ04A1500000G</u>	<u>TJ05A1500000G</u>	<u>TJ06A1500000G</u>	<u>TJ07A1500000G</u>
<u>TJ08A1500000G</u>	<u>TJ09A1500000G</u>	<u>TJ10A1500000G</u>	<u>TJ11A1500000G</u>	<u>TJ12A1500000G</u>	<u>TJ13A1500000G</u>
<u>TJ14A1500000G</u>	<u>TJ15A1500000G</u>	<u>TJ16A1500000G</u>	<u>TJ16A1800000G</u>	<u>TJ02A1000000G</u>	<u>TJ04A1000000G</u>
<u>TJ02A1800000G</u>	<u>TJ03A1000000G</u>	<u>TJ04A1800000G</u>	<u>TJ05A1800000G</u>	<u>TJ06A1000000G</u>	<u>TJ07A1000000G</u>
<u>TJ08A1000000G</u>	<u>TJ09A1000000G</u>	<u>TJ07A1800000G</u>	<u>TJ08A1800000G</u>	<u>TJ06A1800000G</u>	<u>TJ05A1000000G</u>
<u>TJ11A1800000G</u>	<u>TJ13A1000000G</u>	<u>TJ12A1800000G</u>	<u>TJ10A1800000G</u>	<u>TJ11A1000000G</u>	<u>TJ16A1000000G</u>
<u>TJ09A1800000G</u>	<u>TJ13A1800000G</u>	<u>TJ12A1000000G</u>	<u>TJ14A1800000G</u>	<u>TJ15A1000000G</u>	<u>TJ14A1000000G</u>
<u>TJ15A1800000G</u>	<u>TJ10A1000000G</u>	<u>TJ03A1800000G</u>			