


△ P.C.B. LAYOUT  
Top view



△ N=NUMBER OF POLES

Dim L	(N-1)×7.5+6.0
Dim B	(N-1)×7.5

	Dim L	Dim B
2-4p	±0.2	±0.15
5-8p	±0.3	±0.25
9-12p	±0.4	±0.35
13-16p	±0.45	±0.4

SIGN	DATE	DESCRIPTION	APPROVER
△	01/24'07	The Soldering temperature from 245° to 250°	Aaron
△	01/24'07	Add "VDE" stipulation	Aaron
△	01/02'13	change the electrical specification and the dimension from 3.6 to 3.3	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

#### △ Material

- Item ① Contact pin : Brass.Tin plated
- Item ② Wire guard: Stainless steel
- Item ③ Insulator body: Thermoplastic (UL94V-0)
- Item ④ Insulator lever: Thermoplastic (UL94V-0) Natural color
- Item ⑤ Pad board: Thermoplastic (UL94V-0)
- Item ⑥ Insulating cover :Thermoplastic (UL94V-0)

#### △ Electrical cULus VDE △


- Voltage rating: 300VAC 450VAC
- Current rating: 10A 6A
- Wire range: 0.5mm<sup>2</sup>
- Solid wire(AWG): 14-20
- Stranded wire(AWG): 14-20
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV 2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension:

HBxx21x0xxxxG			△ RoHs compliant (lead<4%) In copper Alloy
Poles	Body Color △		
02 2 Poles	0 Black (RAL9005)	000 0 Standard @ Logo	
03 3Poles	2 Red (RAL3001/D)	000 A Standard ANY Logo	
16 16Poles	3 Orange(RAL2011/P)	Any special item by	
	4 Yellow(RAL1018/A)	customer request,	
	5 Green(RAL6018/T)	please contact sales	
	6 Blue (RAL5015/A)	department.	
	8 Grey(RAL7004/P)		
	9 White(RAL1102)		
	C Multiple colors		

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HB - 7.5mm Series (Single wire)			
PART NO.	HBxx21x0xxxxG			DWG NO.	8HB0101
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Da cheng 2013.01.02	Da cheng 2013.01.02		
				SHEET: 01/01	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[HB0221800000G](#) [HB0321800000G](#) [HB0421800000G](#) [HB0521800000G](#) [HB0621800000G](#) [HB0721800000G](#)  
[HB0821800000G](#) [HB0921800000G](#) [HB1021800000G](#) [HB1121800000G](#) [HB1221800000G](#) [HB1321800000G](#)  
[HB1421800000G](#) [HB1521800000G](#) [HB1621800000G](#)