





Dim.A	$N \times 4.0$
Dim.B	$(N-1) \times 4.0$

△	POLES	TOLERANCE
	2P - 3P	-0.20/+0.20

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- ⚠ Item 1 Terminal housing:LCP (UL94 V-0)
- Item 2 Long solder pin: Copper alloy, Matte Tin plated(high temperature)
- Item 3 Short solder pin: Brass ,Matte Tin plated(high temperature)

- Critical dimension: ∇C

NQ xx 2 1 x 0 xxxx G

department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NQ 4.0mm Series (SMT)							
PART NO.		NQxx21x0xxxxG			DWG NO.	8NQ0101			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Airy min 2015/03/27	Airy min 2015/03/27			UNIT: mm	X.	±0.50	
						SCALE: NONE	X.X	±0.30	
				SHEET: 01/01		REV: C	X°	±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>NQ01218000J0G</u>	<u>NQ03210000J0G</u>	<u>NQ01210000J0G</u>	<u>NQ02210000J0G</u>	<u>NQ03211000J0G</u>	<u>NQ03218000J0G</u>
<u>NQ0121000000G</u>	<u>NQ0121800000G</u>	<u>NQ0221000000G</u>	<u>NQ0321000000G</u>	<u>NQ0321100000G</u>	<u>NQ0321800000G</u>
<u>NQ0121100000G</u>	<u>NQ0221100000G</u>	<u>NQ0721000000G</u>	<u>NQ0621000000G</u>	<u>NQ0821000000G</u>	<u>NQ0521000000G</u>
<u>NQ0421000000G</u>	<u>NQ0221800000G</u>				