






Poles	04	06	08	10	12	14	16	18	20	22	24	26
Dim L	8.5	12.0	15.5	19.0	22.5	26.0	29.5	33.0	36.5	40.0	43.5	47.0
Dim B	3.50	7.00	10.5	14.0	17.5	21.0	24.5	28.0	31.5	35.0	38.5	42.0
TOL	±0.15					±0.20						
Poles	28	30	32	34	36	38	40	42	44	46	48	
Dim L	50.5	54.0	57.5	61.0	64.5	68.0	71.5	75.0	78.5	82.0	85.5	
Dim B	45.5	49.0	52.5	56.0	59.5	63.0	66.5	70.0	73.5	77.0	80.5	
TOL	±0.25					±0.30						

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.6.08	Add UL standard	Jacke
△	2009.6.08	The current rating and operating temperature are changed	Jacke
△	2009.6.08	Corrected dimension△ from 2.3mm to 2.5mm	Jacke
△	2010.01.22	The demension is changed from 1.60mm to 1.10mm	Jacke
△	2010.01.22	The demension is changed from 0.40mm to 0.20~0.30mm	Jacke
△	2010.03.31	The material is changed from Brass to Copper	Jacke
△	2010.04.01	The design is changed	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- △ ● Item (a) Short contact pin: Copper Tin plated
- Item (b) Long contact pin: Copper Tin plated
- Item (c) Terminal (housing): Thermoplastic (UL94V-0)
- Item (d) Terminal (cover): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- △ ● Current rating: 8A
- Wire range:
- Solid wire(AWG):
- Stranded wire(AWG):
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 250°C±10°C/5 Sec
- △ ● Safety Approval: cULus

VL xx 1 3 x 1 xxxx G

G: Pb<40000ppm

POLES
04 2x2 CONTACTS
06 2x3 CONTACTS
...
48 2x24 CONTACTS

COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)

000 0 "@ logo
000 A "ANY" logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VL-3.5mm Right -Angle Series "B Type"									
PART NO.	VLxx13x1xxxxG				DWG NO.	8VL0402				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.					Tolerance	
		Jacke 2010.03.31	Jacke 2010.01.22							UNIT: mm
						SCALE: NONE	X.X ±0.30			
					SHEET: 01/01	REV.: D	X.XX ±0.10			
							X° ±1°			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VL0413510000G</u>	<u>VL0613510000G</u>	<u>VL0813510000G</u>	<u>VL1013510000G</u>	<u>VL1213510000G</u>	<u>VL1413510000G</u>
<u>VL1613510000G</u>	<u>VL1813510000G</u>	<u>VL2013510000G</u>	<u>VL2213510000G</u>	<u>VL2413510000G</u>	<u>VL2613510000G</u>
<u>VL2813510000G</u>	<u>VL3013510000G</u>	<u>VL3213510000G</u>	<u>VL3413510000G</u>	<u>VL3613510000G</u>	<u>VL3813510000G</u>
<u>VL4013510000G</u>	<u>VL4213510000G</u>	<u>VL4413510000G</u>	<u>VL4613510000G</u>	<u>VL4813510000G</u>	