






PRODUCT NO.
SEE TABLE




QUICKIE ASSEMBLY



CONTACTS: PHOS BRONZE, FULL HARD
SEE NOTES FOR PLATING

CONTACT BASE:
MOLDING MATERIAL: 30% GLASS FILLED
POLYESTER, FLAME RETARDANT PER
UL 94V-0, COLOR BLUE



mat'l. code				surface ISO 1302	tolerance ISO 1101	projection	product family
U	REDRAW	RLS	6/2/88				QUICKIE
V	M05-0178	MHT	8/11/05	angles	linear	INCH/MM	title
W	M06-0223	ERE	06/12/06	0'±2'	.XXX±.01/XX±0.3 .XXX±.005/XX±0.13 .XXX±.0020/XXX±0.51	scale 5:1	QUICKIE MALE DIP ASSEMBLY
X	M09-0064	MHT	4/10/09	dr	R. SEIPLE	6/2/88	dwg no
		engr	R. DOUTRICH	6/2/88			sheet 1 of 2 size
		chr	R. DOUTRICH	6/2/88			65493 A3
		appd	R. DOUTRICH	6/2/88			type
sheet	revision	X	X				Product Customer Drawing
index	sheet	1	2				

PRODUCT NUMBER	SIZE	DIM A	DIM B	DIM M	CONTACT PLATING
65493-002	2 x 7	16.51/.650	18.24/.718	4.45/.175	NOTE 1
-004	2 x 8	19.05/.750	20.78/.818	4.45/.175	NOTE 1
-006	2 x 7	16.51/.650	18.24/.718	4.45/.175	NOTE 2
-008	2 x 8	19.05/.750	20.78/.818	4.45/.175	NOTE 2
-010	2 x 7	16.51/.650	18.24/.718	4.45/.175	NOTE 3
-012	2 x 8	19.05/.750	20.78/.818	4.45/.175	NOTE 3
-014	2 x 7	16.51/.650	18.24/.718	2.67/.105	NOTE 1
-016	2 x 8	19.05/.750	20.78/.818	2.67/.105	NOTE 2
-018	2 x 7	16.51/.650	18.24/.718	2.67/.105	NOTE 2
-020	2 x 8	19.05/.750	20.78/.818	2.67/.105	NOTE 1
-022	2 x 9	21.59/.850	23.32/.918	4.45/.175	NOTE 1
-024	2 x 9	21.59/.850	23.32/.918	4.45/.175	NOTE 2
75493-026	2 x 9	21.59/.850	23.32/.918	4.45/.175	NOTE 3

PRODUCT NUMBER NOTE 5	SIZE	DIM A	DIM B	DIM M	CONTACT PLATING
65493-002LF	2 x 7	16.51/.650	18.24/.718	4.45/.175	NOTE 1
-004LF	2 x 8	19.05/.750	20.78/.818	4.45/.175	NOTE 1
-006LF	2 x 7	16.51/.650	18.24/.718	4.45/.175	NOTE 4
-008LF	2 x 8	19.05/.750	20.78/.818	4.45/.175	NOTE 4
-010LF	2 x 7	16.51/.650	18.24/.718	4.45/.175	NOTE 3
-012LF	2 x 8	19.05/.750	20.78/.818	4.45/.175	NOTE 3
-014LF	2 x 7	16.51/.650	18.24/.718	2.67/.105	NOTE 1
-016LF	2 x 8	19.05/.750	20.78/.818	2.67/.105	NOTE 4
-018LF	2 x 7	16.51/.650	18.24/.718	2.67/.105	NOTE 4
-020LF	2 x 8	19.05/.750	20.78/.818	2.67/.105	NOTE 1
-022LF	2 x 9	21.59/.850	23.32/.918	4.45/.175	NOTE 1
-024LF	2 x 9	21.59/.850	23.32/.918	4.45/.175	NOTE 4
75493-026LF	2 x 9	21.59/.850	23.32/.918	4.45/.175	NOTE 3

NOTES:

- 1.27 μ /50 μ "MIN Ni UNDERPLATE OVER ENTIRE TERMINAL AND .76 μ /30 μ "MIN Au IN DISCONNECT AREA ONLY.
- 3.81 μ /150 μ " MIN TIN/LEAD 93/7 OVER ENTIRE TERMINAL
- 1.27 μ /50 μ "MIN Ni UNDERPLATE OVER ENTIRE TERMINAL AND 1.27/50 μ "MIN Au IN DISCONNECT AREA ONLY.
- LEAD FREE OPTION: 3.81 μ /150 μ " MIN PURE TIN OVER ENTIRE TERMINAL
- PART NUMBER WITH "LF" SUFFIX AT THE END ARE LEAD FREE OPTION.
- IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.

mat'l. code		surface		tolerance	projection	product family	
-		ISO 1902		ISO 406		QUICKIE	
-		ISO 1101		ISO 1101		title	
ltr	ecr no	dr	date	tolerances unless otherwise specified		QUICKIE MALE DIP ASSEMBLY	
x				angles	linear	INCH/MM	
						scale 5:1	
				dr	R. SEIPLE	6/2/88	
				engr	R. DOUTRICH	6/2/88	
				chr	R. DOUTRICH	6/2/88	
				appd	R. DOUTRICH	6/2/88	
sheet	revision			FCJ		dwg no	
index	sheet					sheet 2 of 2 size	
						65493 A3	
						type Product Customer Drawing	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[65493-006](#) [65493-006LF](#) [65493-002LF](#) [65493-008LF](#) [65493-004LF](#) [65493-002](#)