





SIGN	DATE	DESCRIPTION	APPROVER
△	8/07'06	Added VDE standard	梁仁松
△	1/27'07	Soldering temperature changed from 245° to 250°	Tony
△	2009.10.26	The material is changed from Brass to Copper	Jacke
△	2009.10.26	The operating temperature is changed	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



P.C.B LAYOUT

Dim.L = (N-1) x 3.5+4.9  
Dim.B = (N-1) x 3.5  
N= number of poles

poles Dim.	2P-6P	7P-12P	13P-18P	19P-24P
Dim.L	±0.15	±0.20	±0.25	±0.30
Dim.B	±0.15	±0.20	±0.25	±0.30

Material:

- △ ● Item ③ Male contact pin: Copper Tin plated
- Item ⑥ Terminal (housing): Thermoplastic (UL94V-0)

- △ Electrical: cULus /VDE
  - Voltage rating: 300V/300V
  - Current rating: 8A/10A
  - Withstanding Voltage: 1.6 KV/2.5KV
  - △ ● Operating temperature: -40°C to +115°C
  - △ ● Soldering temperature: 250°C±10°C/5 Sec
  - Safety Approval: cULus VDE

VK xx 1 1 x 0 xxxx G

No. OF POLES  
02: 2 POLES  
:  
:  
24: 24 POLES

COLOR  
0 Black (RAL9005)  
2 Red (RAL3001/D)  
3 Orange(RAL2011/P)  
4 Yellow(RAL1018/A)  
5 Green(RAL6018/T)  
6 Blue (RAL5015/A)  
8 Grey(RAL7035/D)

G: Pb<40000ppm  
0000: "@" Logo (Standard)  
000A: "ANYTEK" Mark  
Any special item by  
customer request.  
please contact sales  
department.

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VK - 3.5mm Series (without flange)			
PART NO.	VKxx11x0xxxxG			DWG NO. 8VK0001
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.
		Jacke 2009.10.27	Jacke 2009.10.27	
		SHEET: 01/01		REV.: F
		UNIT: mm		Tolerance
		SCALE: NONE		X. ±0.50
				X.X ±0.30
				X.XX ±0.10
				X° ±1°

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

<a href="#"><u>VK2411500000G</u></a>	<a href="#"><u>VK0611500000G</u></a>	<a href="#"><u>VK0911500000G</u></a>	<a href="#"><u>VK1611500000G</u></a>	<a href="#"><u>VK1111500000G</u></a>	<a href="#"><u>VK0511500000G</u></a>
<a href="#"><u>VK2011500000G</u></a>	<a href="#"><u>VK0711500000G</u></a>	<a href="#"><u>VK2211500000G</u></a>	<a href="#"><u>VK2311500000G</u></a>	<a href="#"><u>VK0211500000G</u></a>	<a href="#"><u>VK1411500000G</u></a>
<a href="#"><u>VK2111500000G</u></a>	<a href="#"><u>VK1211500000G</u></a>	<a href="#"><u>VK0411500000G</u></a>	<a href="#"><u>VK1911500000G</u></a>	<a href="#"><u>VK0311500000G</u></a>	<a href="#"><u>VK1511500000G</u></a>
<a href="#"><u>VK1811500000G</u></a>	<a href="#"><u>VK0811500000G</u></a>	<a href="#"><u>VK1311500000G</u></a>	<a href="#"><u>VK1711500000G</u></a>	<a href="#"><u>VK1011500000G</u></a>	