

SPF™ Low Loss, Low PIM Coaxial Cables

Fire Retardant Low Loss, Low PIM Cable Assemblies

- -160 dBc PIM for optimal system performance
- UL listed, type CMR (riser) UL file #E-170516
- Super flexible for ease of installation
- Corrugated copper outer conductor providing greater than 100dB Shielding
- Durable fire retardant, low smoke polyolefin outer jacket is suitable for outdoor use

**Major
Carrier
Approved!**


ISO 9001 Certified



SPF-250, SPF-375, SPF-500 50 Ohm low loss, low PIM cable assemblies


- Available in any required connector configuration and length
- Large selection of standard configurations for quick delivery
- Check inventory at StockCheck on our website
- 100% tested for static and dynamic PIM, VSWR and insertion loss
- Serial marker band includes PIM, VSWR and IL test data which is retained and accessible on the Times website
- 10 year Times Microwave warranty

Typical VSWR




SPF250NMNML0M

Dynamic PIM Test Results



SPF™ Coaxial Cables



Cable Construction

Inner Conductor:

- SPF-250: Solid bare copper
- SPF-375: BCCAL
- SPF-500: BCCAL

Dielectric: Foam Polyethylene

Outer Conductor: Seam welded corrugated copper tube


Jacket: UV and sunlight resistant black flame retardant, non halogen, polyethylene

Physical Specifications		SPF-250		SPF-375		SPF-500	
Jacket: Extruded Polyethylene; OD: in(mm)		0.300	(7.7)	0.425	(10.8)	0.525	(13.4)
Outer Conductor: Corrugated Copper Tube; OD: in(mm)		0.250	(6.3)	0.380	(9.6)	0.472	(12.1)
Dielectric: Foam PE; OD: in(mm)		0.190	(4.8)	0.285	(7.1)	0.370	(9.4)
Center Conductor: Solid BCCAl; OD: in(mm)		0.075	(1.9)	0.110	(2.8)	0.142	(3.6)
Bend Radius: in(mm)		1.0	(25)	1.7	(2.3)	2.0	(51)
Bending Moment: ft-lbs (N-m)		1.84	(2.5)	2.07	(2.8)	3.25	(4.4)
Tensile Strength: lb (kg)		150	(68.2)	175	(79.5)	210	(95.5)
Flat Plate Crush Strength: lb/in (kg/mm)		100	(1.8)	100	(1.8)	110	(2.0)
Weight: lbs/1000 ft (kg/km)		46	(67)	78	(120)	140	(210)
Environmental Specifications							
Installation Temperature Range °F/°C		-25/+60°C		-25/+60°C		-25/+60°C	
Storage Temperature Range °F/°C		-70/+85°C		-70/+85°C		-70/+85°C	
Operating Temperature Range °F/°C		-40/+85°C		-40/+85°C		-40/+85°C	
Electrical Specifications							
Velocity of Propagation: %		84		84		84	
Impedance: Ohms		50		50		50	
Capacitance: pF/ft (pF/m)		24.2	(79.4)	24.3	(79.7)	25.2	(82.7)
Inductance: μH/ft (uH/m)		0.61	(0.200)	0.61	(0.200)	0.63	(0.205)
Shielding Effectiveness: dB		>100		>100		>100	
Center Conductor DC Resistance: Ohms/1000 ft/(km)		3.00	(9.84)	1.30	(4.26)	0.82	(2.70)
Shield DC Resistance: Ohms/1000 ft (km)		2.00	(6.56)	1.52	(4.98)	1.00	(3.28)
Attenuation & Average Power @ MHz		dB/100 ft (dB/100m) kW		dB/100ft (dB/100m) kW		dB/100ft (dB/100m) kW	
450		4.1	(13.3) 1.01	2.8	(9.1) 2.11	2.2	(7.2) 2.63
700		5.1	(17.1) 0.81	3.5	(11.5) 1.67	2.8	(9.1) 2.07
850		5.7	(18.7) 0.73	3.9	(12.8) 1.50	3.1	(10.2) 1.87
1900		8.9	(29.2) 0.47	6.0	(19.7) 0.97	4.8	(15.7) 1.20
2100		9.4	(30.8) 0.45	6.4	(21.0) 0.92	5.2	(17.1) 1.14
2300		9.9	(32.5) 0.43	6.7	(22.0) 0.87	5.6	(18.4) 1.08
2400		10.1	(33.1) 0.42	6.9	(22.6) 0.85	5.7	(18.7) 1.05
4900		15.0	(49.2) 0.28	10.5	(34.4) 0.85	9.6	(31.5) 0.70
5800		16.5	(54.1) 0.26	11.6	(38.0) 0.52	10.9	(35.8) 0.63
Connectors (solder body) (connectors with BLK suffix packed 100 pieces per bulk pack)							
N Male Straight		TC-SPO250-NM-LP (3190-6053BLK)		TC-SPO375-NM-LP (3190-6059BLK)		TC-SPO500-NM-LP (3190-6004BLK)	
N Male Right Angle		TC-SPO250-NM-RA-LP (3190-6055BLK)		TC-SPO375-NM-RA-LP (3190-6061BLK)		TC-SPO500-NM-RA-LP (3190-6065BLK)	
N Female		TC-SPO250-NF-LP (3190-6054BLK)		TC-SPO375-NF-LP (3190-6060BLK)		TC-SPO500-NF-LP (3190-6005BLK)	
7-16 DIN Male Straight		TC-SPO250-716M-LP (3190-6056BLK)		TC-SPO375-716M-LP (3190-6062BLK)		TC-SPO500-716M-LP (3190-6066BLK)	
7-16 DIN Male Right Angle		TC-SPO250-716M-RA-LP (3190-6058BLK)		TC-SPO375-716M-RA-LP (3190-6064BLK)		TC-SPO375-716M-RA-LP (3190-6068BLK)	
7-16 DIN Female Straight		TC-SPO250-716F-LP (3190-6057BLK)		TC-SPO375-716F-LP (3190-6063BLK)		TC-SPO500-716F-LP (3190-6067BLK)	
SMA Male Straight		TC-SPP250-SM-LP (3190-6182BLK)		N/A		N/A	

- Jumpers available in any length with most popular connector combinations.

SPF™ Coaxial Cables

Smart Part Number Key for Low PIM Jumpers



SPF™ Coaxial Cables

About TIMES MICROWAVE SYSTEMS

Times Microwave Systems, was founded in 1948 as the Times Wire and Cable Company. Today, the company specializes in the design and manufacture of high performance flexible, semi-flexible and semi-rigid coaxial cable, connectors and cable assemblies. With over 60 years of leadership in the design, development, and manufacture of coaxial products for defense microwave systems, Times Microwave Systems is the acknowledged leader, offering high tech solutions for today's most demanding applications.

Cable assemblies from Times Microwave Systems are used as interconnects for microwave transmitters, receivers, and antennas on airframes, missiles, ships, satellites, and ground based communications systems, and as leads for test and instrumentation applications.

As a highly specialized and technically focused company, Times Microwave Systems has been able to continually meet the challenges of specialty engineered transmission lines for both the military and commercial applications, drawing upon our:

- Thousands of unique cable and connector designs
- Exceptional RF and microwave design capability
- Precise material and process controls
- Unique in-house testing capabilities including RF shielding/leakage, vibration, moisture/vapor sealing, phase noise and flammability
- Years of MIL-T-81490, MIL-C-87104, and MIL-PRF-39012 experience
- ISO 9001 Certification

In 2010, Times Microwave Systems introduced its Times-Protect™ line of lightning and surge protection solutions to address the challenging needs of wireless systems in the 21st century.

With over 60 years of Times Microwave Systems aerospace cable and connector technology experience and unparalleled design expertise, Times Microwave Systems' staff of Field Applications Engineers can help to provide the right solution for your interconnect applications.



World Headquarters: 358 Hall Avenue, Wallingford, CT 06492 • Tel: 203-949-8400, 1-800-867-2629 Fax: 203-949-8423

International Sales: +1 203-949-8503 • +1 800-867-2629

China Sales: TMC Building 4, No. 318 Yuanshan Road, Xinzhuang Industrial Park, Shanghai, China 201108 Tel: 86-21-5176-1209 Fax: 86-21-64424098

www.timesmicrowave.com

© 2015, Times Microwave Systems, Wallingford, CT 06492

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[SPF-250](#) [SPF-375](#) [SPF-500](#)