




REV	ECN	APP'D
–	4057	JT 8/7/00
A	4059	JT 8/8/00
B	–	AP 2/7/01



#### NOTES:

- MATERIALS—  
INSULATOR BODY: POLYETHERIMIDE PER MIL-P-46184  
SEALING GROMMET: SILICONE RUBBER PER ZZ-R-765  
INTERNAL CONTACTS: COPPER ALLOY, GOLD PLATE PER MIL-G-45204  
RETAINER CLIPS: BERYLLIUM COPPER  
DIODES: JANTX1N5622
- PART REQUIRES SIZE 16/20 PIN CONTACTS, M39029/1-101, SUPPLIED WITH DIRECT SHIPMENT
- PART MEETS ENVIRONMENTAL AND ELECTRICAL REQUIREMENTS PER MIL-T-81714 (SUBJECT TO LIMITATIONS OF INTERNAL DIODES)—  
TEMPERATURE: –65°C TO 200°C  
INSULATION RESISTANCE: 5000 MEGOHMS MIN @ 25°C  
DIELECTRIC WITHSTANDING VOLTAGE: 1500Vrms AT SEA LEVEL  
200Vrms AT 100,000 FT ALTITUDE  
CONTACT CURRENT RATING: 7.5 AMPS  
VIBRATION AND SHOCK: MIL-T-81714, PARAGRAPH 3.5.8 & 3.5.9

DIMENSIONS ANSI Y14.5M UNITS: INCHES ACAD FILE	TOLERANCES .XX ±.01 .XXX ±.005 ANGLES ±2°	PROJECTION 	SPECIFICATION DRAWING		 <div>TITLE WIRE SPLICE, DOUBLE ELECTRONIC, DIODE SIZE 20, ANODE BUS</div>					
ORIGINAL			ENGR A. PATRIE 7/19/00		SIZE A		DWG NO. TJSE20707		REV B	
			CHKD A. PATRIE 8/8/00							
			APPD J. TON 8/8/00		CODE: 58982		SCALE: 2X		SHEET 1 OF 1	
			THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF PCD, INC. PEABODY, MA, USA							

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[TJSE20707](#)