




P.C.B LAYOUT



SECTION A-A

N = Number of poles
 Dim A=Nx5.0+3.2
 Dim B=Nx5.0+0.7
 Dim C=(N-1)x5.0

	Dim A	Dim B	Dim C
2-6p	±0.20	+0.15 -0	±0.20
6-12p	±0.30	+0.3 -0	±0.30
12-24p	±0.40	+0.4 -0	±0.40

SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

Material:

- Item a :Male contact pin: Copper Tin plated
- Item b :Terminal(housing): Thermoplastic (UL94V-0)

Electrical: cULus

- Voltage rating: 300V
- Current rating: 8A
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: cULus

NC xx 7 1 x 1 xxxx G

- | | | |
|-------------|---------------------|--|
| 02 2 poles | 0 Black (RAL9005) | any special item by customer request, please contact sales department. |
| 03 3 poles | 2 Red (RAL3001/D) | |
| | 3 Orange(RAL2011/P) | |
| 24 24 poles | 4 Yellow(RAL1018/A) | |
| | 5 Green(RAL6018/T) | |
| | 6 Blue (RAL5015/A) | |
| | 8 Grey(RAL7035/D) | |
| | G: Pb<40,000ppm | |

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		NC 5.0mm Right-angle Series			
PART NO.	NCxx71x1xxxxG			DWG NO.	8NC0002
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Runner 2010.08.16	Runner 2010.08.16		Tolerance
					X. ±0.50
					X.X ±0.30
				UNIT: mm	X.XX ±0.10
				SCALE: 2/1	X° ±1°
				SHEET: 01/01	REV.: B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>NC0271810000G</u>	<u>NC0371810000G</u>	<u>NC0471810000G</u>	<u>NC0571810000G</u>	<u>NC0671810000G</u>	<u>NC0771810000G</u>
<u>NC0871810000G</u>	<u>NC0971810000G</u>	<u>NC1071810000G</u>	<u>NC1171810000G</u>	<u>NC1271810000G</u>	<u>NC1371810000G</u>
<u>NC1471810000G</u>	<u>NC1571810000G</u>	<u>NC1671810000G</u>	<u>NC1771810000G</u>	<u>NC1871810000G</u>	<u>NC1971810000G</u>
<u>NC2071810000G</u>	<u>NC2171810000G</u>	<u>NC2271810000G</u>	<u>NC2371810000G</u>	<u>NC2471810000G</u>	