





REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
K	UPDATE DESCRIPTION	APR06/16	JS



U10 - D038 - X X X X

- OPTIONS**
- 0** = STANDARD CONSTRUCTION (24G) WITH TAPE & REEL PACKAGING
- 1** = NO RESONANCE DAMPING FEATURE (12G) WITH TAPE & REEL PACKAGING
- LATCH PTH PIN LENGTH OPTIONS**
- 0** = 1.50
- 2** = 2.20
- 3** = 3.00
- 4** = 4.20
- CONTACT PLATING OPTIONS**
- 2** = 30 MICROINCHES OF GOLD ON MATING END WITH 100 MICROINCHES MINIMUM OF MATTE TIN ON SOLDER TERMINATION. 50-75 MICROINCHES OF NICKEL UNDERPLATE ALL OVER
- 3** = 15 MICROINCHES OF GOLD ON MATING END WITH 100 MICROINCHES MINIMUM OF MATTE TIN ON SOLDER TERMINATION. 50-75 MICROINCHES OF NICKEL UNDERPLATE ALL OVER

- NOTES:
- 1) MATERIAL:
- HOUSING: SOLDER REFLOW PROCESS COMPATIBLE LCP, UL94V-0
- CONTACTS: HIGH PERFORMANCE COPPER ALLOY
- LATCH: PHOSPHOR BRONZE
- RESONANCE DAMPENING FEATURE: SEMI-CONDUCTIVE POLYMER
- 2)RoHS COMPLIANT



UNLESS SPECIFIED OTHERWISE		DRAWN	A.ALIM	DEC04/13
PRIMARY UNITS	MILLIMETERS	CHECKED	BA P	SEP12/14
SECONDARY	INCHES	M.E. APP'D		
REFERENCE IN PARENTHESES		Q.A. APP'D		
GENERAL TOLERANCES		DWG APPR.	ZLJ	DEC04/13
1 DECIMAL PLACE	±0.35	ENG. REL. NO.	ECN TBD	
2 DECIMAL PLACES	±0.25	REF.		
3 DECIMAL PLACES	±0.15	THIRD ANGLE PROJECTION		
ANGULAR DEGREES	±2°			

Amphenol High Speed Interconnects A Division of Amphenol Corp. www.amphenolcanada.com			
ULTRAPORT SLIMSAS™ 4X24 VERTICAL RECEPTACLE WITH PIN INSIDE LATCH			
DWG. NO.			REV
P-U10-D038-XXXX			K
DWG. ID NO.	03554	DWG SIZE:	C
SCALE:	7	SHEET	1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[U10-D038-300T](#) [U10-D038-200T](#) [U10-D038-201T](#) [U10-D038-301T](#)