







SIGN	DATE	DESCRIPTION	APPROVER
△	02/07'06	Part No. changed	Tony
△	8/16'06	Added TUV standard	Tony
△	12/02'08	Flange screw changed from "-" to "+/-"	Tony
△	2010.03.23	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item a Clamp: Steel zinc plated.
- Item b Terminal screw: Steel Zinc plating "-" slot type
- Item c Female contact: PhBz Tin plated
- Item d With flange screw: Steel zine plated M2.5 "+/-" slot type
- Item e Terminal (Up body): Thermoplastic (UL94V-0)
- Item f Terminal (Down body): Thermoplastic (UL94V-0)
- Item g Clampage: Steel Zinc plated
- △ Electrical cULus/TUV
- Voltage rating: 300VAC/300VAC
- Current rating: 20A/20A
- Wire range: 0.34-2.5mm²
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In / 0.4Nm
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV/2.5KV
- Operating temperature: -40°C to +115°C
- Safety approval: cULus TUV

△ ● Part No.:

VM xx 5 5 x 2 xxxx G

POLES

02 pole

24 pole

Color

- 0 Black (RAL9005)
- 2 Red (RAL3001/D)
- 3 Orange(RAL2011/P)
- 4 Yellow(RAL1018/A)
- 5 Green(RAL6018/T)
- 6 Blue (RAL5015/A)
- 8 Grey(RAL7035/D)

G: Pb<40000ppm

0000: Standard
(Steel screw plating Cr^{III})
000A: "ANYTEK" Mark
Any special item by
customer request.
please contact sales
department.

POLE		2	3	4	5	6	7	8	9	10	11	12
A		10.66	15.74	20.82	25.90	30.98	36.06	41.14	46.22	51.30	56.38	61.46
B		5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88
Tol.	±0.20						±0.25					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	66.54	71.62	76.70	81.78	86.86	91.94	97.02	102.10	107.18	112.26	117.34	122.42
B	60.96	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84
Tol.	±0.30						±0.40					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VM 5.08mm W/Flange Series										
PART NO.	VMxx55x2xxxxG				DWG NO.	8VM0102					
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.						Tolerance	
		Jacke 2010.03.23	Jacke 2010.03.23							UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30					
				SHEET: 01/01	REV.: F	X.XX ±0.10					
						X° ±1°					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>VM0255520000G</u>	<u>VM0355520000G</u>	<u>VM0455520000G</u>	<u>VM0555520000G</u>	<u>VM0655520000G</u>	<u>VM0755520000G</u>
<u>VM0855520000G</u>	<u>VM0955520000G</u>	<u>VM1055520000G</u>	<u>VM1155520000G</u>	<u>VM1255520000G</u>	<u>VM1355520000G</u>
<u>VM1455520000G</u>	<u>VM1555520000G</u>	<u>VM1655520000G</u>	<u>VM1755520000G</u>	<u>VM1855520000G</u>	<u>VM1955520000G</u>
<u>VM2055520000G</u>	<u>VM2155520000G</u>	<u>VM2255520000G</u>	<u>VM2355520000G</u>	<u>VM2455520000G</u>	<u>VM2355020000G</u>
<u>VM1855820000G</u>	<u>VM1255820000G</u>	<u>VM1755020000G</u>	<u>VM2055820000G</u>	<u>VM1555820000G</u>	<u>VM2155820000G</u>
<u>VM2255820000G</u>	<u>VM2455820000G</u>	<u>VM1455020000G</u>	<u>VM1855020000G</u>	<u>VM2055020000G</u>	<u>VM2155020000G</u>
<u>VM1955020000G</u>	<u>VM2255020000G</u>	<u>VM1955820000G</u>	<u>VM1355020000G</u>	<u>VM2455020000G</u>	<u>VM2355820000G</u>
<u>VM0255020000G</u>	<u>VM0555820000G</u>	<u>VM0455820000G</u>	<u>VM0255820000G</u>	<u>VM0555020000G</u>	<u>VM0355020000G</u>
<u>VM0755020000G</u>	<u>VM0855020000G</u>	<u>VM1155020000G</u>	<u>VM1655820000G</u>	<u>VM1555020000G</u>	<u>VM0655020000G</u>
<u>VM1255020000G</u>	<u>VM0755820000G</u>	<u>VM0955820000G</u>	<u>VM0855820000G</u>	<u>VM1055020000G</u>	<u>VM1655020000G</u>
<u>VM0955020000G</u>	<u>VM1155820000G</u>	<u>VM0655820000G</u>	<u>VM1355820000G</u>	<u>VM1755820000G</u>	<u>VM0355820000G</u>
<u>VM0455020000G</u>	<u>VM1455820000G</u>	<u>VM1055820000G</u>			