



T H E R M O M E T R I C S
A C O M M I T M E N T T O E X C E L L E N C E

Type PTO Series

Thermometrics PTC Thermistors



Description

Thermometrics PTO series consists of a range of radially-wire bare PTC disc thermistors.

Features

- Low cost solid state sensor
- Available in a broad range of resistances, transition temperatures and voltage ratings
- Exhibits large positive increases in resistance with temperature
- Resistance/temperature characteristic is infinitely repeatable and has no hysteresis associated with its action
- Proven quality and reliability over many years of manufacturing

Applications


- Current regulation
- Circuit protection
- Temperature measurement and control

Amphenol
Advanced Sensors

Operating Voltage, V_{max}	Part Number	Replacement for	R @ 25°C ($\pm 30\%$) Ω	Switch Temperature, T_b	A (max) mm	B (max) mm	C (ref) mm	D (ref) mm	L (min) mm
12	YQS5893PTO	YS5893PTO (RL5305-2.5-110-12-PTO)	2.5	120°C	15.24	4.06	5.0	0.6	25
12	YQS5898PTO	YS5898PTO (RL3005-25-110-12-PTO)	25	120°C	8.89	3.81	5.0	0.6	25
25	YQS5745PTO	YS5745PTO (RL3006-50-30-25-PTO)	50	43°C*	8.89	3.81	5.0	0.5	25
25	YQS5749PTO	YS5749PTO (RL3006-50-80-25-PTO)	50	80°C	8.89	3.81	5.0	0.5	25
25	YQS5750PTO	YS5750PTO (RL3006-50-90-25-PTO)	50	90°C	8.89	3.81	5.0	0.5	25
25	YQS5751PTO	YS5751PTO (RL3006-50-100-25-PTO)	50	100°C	8.89	3.81	5.0	0.5	25
120	YQS5917PTO	YS5917PTO (RL6010-20-120-120-PTO)	20	120°C	16.51	5.84	8.38	0.8	38.1
120	YS5918PTO	RL5510-25-60-120-PTO	25	60°C	15.24	5.59	8.38	0.8	38.1
120	YS5921PTO	RL2510-200-110-120-PTO	200	120°C	7.62	5.08	3.81	0.6	38.1
240	YQS5925PTO	YS5925PTO (RL6015-100-120-240-PTO)	100	120°C	16.51	6.86	8.38	0.8	38.1
240	YQS5930PTO	YS5930PTO (RL3020-3000-100-240-PTO)	3K	110°C	8.89	7.87	6.35	0.8	25
480	YQS5934PTO	YS5934PTO (RL3020-5K-100-480-PTO)	5K	102°C	8.89	7.62	6.35	0.8	25

*Resistance = 2 x Resistance at 25°C

Mechanical Specifications



Electrical Specifications

Ambient Temperature Range

At Storage: -25 to +155°C

At Maximum Voltage: +10 to +55°C

Construction

Bare ceramic disc
Thick silver film electrodes
Uninsulated leadwires

Terminations

Straight type, tin coated copper wire

Amphenol
Advanced Sensors

www.amphenol-sensors.com

© 2014 Amphenol Corporation. All Rights Reserved. Specifications are subject to change without notice. Other company names and product names used in this document are the registered trademarks or trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[RL3020-3000-100-240-PTO](#) [RL3312-200-110-50-PTO](#) [RL3020-5K-100-480-PTO](#) [RL3020-200-110-240-PTU](#)
[RL3312-200-110-50-PTF](#) [RL3006-50-30-25-PTO](#) [RL3006-50-80-25-PTO](#) [RL3006-50-90-25-PTO](#) [RL5305-2.5-110-12-](#)
[PTO](#) [RL6010-20-120-120-PTO](#) [RL6015-100-120-240-PTO](#) [RL7020-1K-100-480-PTO](#) [YQS5893PTO](#) [YQS5745PTO](#)
[YQS5749PTO](#) [YQS5751PTO](#) [YS5921PTO](#) [YQS5898PTO](#) [YQS5934PTO](#) [YQS5917PTO](#) [YQS5750PTO](#)
[YQS5925PTO](#) [YQS5930PTO](#) [YQS5746PTO](#) [YS5678](#) [YS5631](#)