




LAY-OUT
P.C.B.-HOLE



PERFORMANCE CHARACTERISTICS

- CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)
- RATED VOLTAGE : 500 V AC (CONT /CONT)
- OPERATING TEMPERATURE : -55°C TO 125°C
- CONTACT RESISTANCE 20 mΩ MAX
- INSERTION FORCE : 0.75N MAX/CONT
- EXTRACTION FORCE : 0.15N MIN/CONT
- INSULATION RESISTANCE : 10⁴ MΩ MIN

NOTES

1. " " LEAD FREE INDICATOR : LF=LEAD FREE
- PERFORMANCE LEVEL INDICATION
(REF DWG NO.BSC.201844.003)
2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED.
3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING : BS.A.201572.001
4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	DG05-0322	Kason	05-09-05
B	DG06-0019	Kason	13-01-06
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

Material			Spec ref			
Mat code			✓	tolerance 1DEC ±0.2 1DEC 2DEC ±0.1 2DEC ANGLES ±1°HOEKEN	projection 	 MM
Heat treat						
Plating/Finish						
Dr	Kason Luo	05-09-05	size A4			Scale 1.500
Eng	Colins Lu	05-09-05	Product family MILLIPACS			
Chr	Victor Lin	05-09-05	Model Name			ECN
Appr	Joseph Hsia	05-09-05	Model Revision			REL Level
		title MPACS 8+2R RA RCP CONN TYPE F /UPPER SHIELDED			dwg no BSC201420006	
Rev. B						
Pro/E file	catalog	HM2B89PE810F----			CUSTOMER DRAWING.	
sheet 1 of 1						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[HM2R89PE810FN9LF](#)