

SIGN	DATE	DESCRIPTION	APPROVER
△	2010.03.31	Add the 2p mark	Jacke
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:





- Item ① Terminal(up body): Thermoplastic (UL94V-0)
- Item ② Terminal(down body): Thermoplastic (UL94V-0)
- Item ③ Female contact: PhBz ,Tin plated
- Item ④ Clamp: Brass(CuZn) Ni plated
- Item ⑤ Terminal screw: Steel Zinc plating "- " slot type
- Item ⑥ With flange screw: M2.5 Steel Zinc plated. "+/-" slot type

Electrical: cULus

- Voltage rating:300 V
- Current rating:20 A
- Wire range:
- Solid wire(AWG):12-22
- Stranded wire(AWG):12-22
- Torque:4 Lb-In
- Screw:M3
- Wire strip length:7-8 mm
- Withstanding Voltage: 1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval: cULus

EM xx 7 1 x 2 xxxx G

No. OF POLES		G: Pb<40000ppm
02: 2 POLES		
:		
24: 24 POLES		
	Color	0000: "@" Logo (Standard)
	0 Black (RAL9005)	000A: "ANYTEK" Mark
	2 Red (RAL3001/D)	Any special item by
	3 Orange(RAL2011/P)	customer request.
	4 Yellow(RAL1018/A)	please contact sales
	5 Green(RAL6018/T)	department.
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	



POLE		2	3	4	5	6	7	8	9	10	11	12
A		10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00	60.00
B		5.00	10.00	15.00	20.00	25.00	30.00	35.00	40.00	45.00	50.00	55.00
Tol.		±0.15					±0.20					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00	120.00
B	60.00	65.00	70.00	75.00	80.00	85.00	90.00	95.00	100.00	105.00	110.00	115.00
Tol.		±0.25					±0.30					

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	EM-5.0 Series With flange						
PART NO.	EMxx71x2xxxxG			DWG NO.	8EM0201		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Jacke 2010.04.01	Jacke 2010.04.01		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: C	X.XX ±0.10	
						X° ±1°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>EM0271520000G</u>	<u>EM0371520000G</u>	<u>EM0471520000G</u>	<u>EM0571520000G</u>	<u>EM0671520000G</u>	<u>EM0771520000G</u>
<u>EM0871520000G</u>	<u>EM0971520000G</u>	<u>EM1071520000G</u>	<u>EM1171520000G</u>	<u>EM1271520000G</u>	<u>EM1371520000G</u>
<u>EM1471520000G</u>	<u>EM1571520000G</u>	<u>EM1671520000G</u>	<u>EM1771520000G</u>	<u>EM1871520000G</u>	<u>EM1971520000G</u>
<u>EM2071520000G</u>	<u>EM2171520000G</u>	<u>EM2271520000G</u>	<u>EM2371520000G</u>	<u>EM2471520000G</u>	