

SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Insulating body: Thermoplastic (UL94V-0)
- Item ② contact pin: Brass Tin plated.
- Item ③ Insulating lever : Thermoplastic (UL94V-0)
- Item ④ Spring clamp : Stainless steel
- Item ⑤ Side Cover : Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-20
- Stranded wire(AWG): 16-20
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C ±10°C/5 Sec

HB xx 41 x 0 xxxx G

No. OF POLES

02: 2 POLES
24: 24 POLES

COLOR

0: Black
2: RED
3: ORANGE
5: GREEN (RAL6018/T)
8: GREY

G: Pb<40000ppm




0000 Standard @ Logo
000A Standard ANY Logo
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HB 3.96 mm With lever Series				
PART NO.	HBxx41x0xxxxG			DWG NO.	8HB0601
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Kind 2009.11.03	Tony 2008.12.16		Tolerance
					X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
				SHEET: 01/01	REV.: B



P.C.B Layout

POLE		2	3	4	5	6	7	8	9	10	11	12
Dim.L		7.92	11.88	15.84	19.80	23.76	27.72	31.68	35.64	39.60	43.56	47.52
Dim.P		3.96	7.92	11.88	15.84	19.80	23.76	27.72	31.68	35.64	39.60	43.56
Tol.	±0.15						±0.25					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
Dim.L	51.48	55.44	59.40	63.36	67.32	71.28	75.24	79.20	83.16	87.12	91.08	95.04
Dim.P	47.52	51.48	55.44	59.40	63.36	67.32	71.28	75.24	79.20	83.16	87.12	91.08
Tol.	±0.30						±0.40					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

<u>HB0241800000G</u>	<u>HB0341800000G</u>	<u>HB0441800000G</u>	<u>HB0541800000G</u>	<u>HB0641800000G</u>	<u>HB0741800000G</u>
<u>HB0841800000G</u>	<u>HB0941800000G</u>	<u>HB1041800000G</u>	<u>HB1141800000G</u>	<u>HB1241800000G</u>	<u>HB1341800000G</u>
<u>HB1441800000G</u>	<u>HB1541800000G</u>	<u>HB1641800000G</u>	<u>HB1741800000G</u>	<u>HB1841800000G</u>	<u>HB1941800000G</u>
<u>HB2041800000G</u>	<u>HB2141800000G</u>	<u>HB2241800000G</u>	<u>HB2341800000G</u>	<u>HB2441800000G</u>	