



P.C.B LAYOUT



N=Number of contacts




SIGN	DATE	DESCRIPTION	APPROVER
△			
△			
△			

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

#### Material:

- Item 1 Terminal housing: Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass ,Ni plated
- Item 3 Wire guard solder pin: Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

#### Electrical cULus

- Voltage rating: 300V
- Current rating: 16A
- Wire range:
- Solid wire(AWG): 12-28
- Stranded wire(AWG): 12-28
- Torque: 3.5Lb-In
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 

VI xx 21 x 3 xxxx G

04 4 CONTACTS  
05 5 CONTACTS  
...  
24 24 CONTACTS

0 Black  
5 Green  
6 Blue  
8 Light Grey

0000:"@Logo (Standard )  
000A:"ANYTEK"Logo  
Any special item by  
customer request,  
please contact sales  
department.


Pb < 40,000ppm  
(RoHS)

Poles	02	03	04	05	06	07	08	09	10	11	12	13
Dim A			20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04
Dim B			15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
TOL	±0.10				±0.15				±0.20			
Poles	14	15	16	17	18	19	20	21	22	23	24	
Dim A	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92	
Dim B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	
TOL	±0.20		±0.25				±0.30					

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VI 5.08 SERIES 4P-24P 90° wire inlet Vertical-solid block(without cover)									
PART NO.	Vlxx21x3xxxxG				DWG NO.	8VI0303				
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.					Tolerance	
		Aaron 2009.09.16	Aaron 2009.09.16						UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30				
						X.XX ±0.10				
						X° ±1°				

SHEET: 01/01

REV.: B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[VI0421530000G](#) [VI0521530000G](#) [VI0621530000G](#) [VI0721530000G](#) [VI0821530000G](#) [VI0921530000G](#)  
[VI1021530000G](#) [VI1121530000G](#) [VI1221530000G](#) [VI1321530000G](#) [VI1421530000G](#) [VI1521530000G](#)  
[VI1621530000G](#) [VI1721530000G](#) [VI1821530000G](#) [VI1921530000G](#) [VI2021530000G](#) [VI2121530000G](#)  
[VI2221530000G](#) [VI2321530000G](#) [VI2421530000G](#)