






FCIconnect.com

Copyright FCI



ORDERING INFORMATION

C	D	1	5	S	1	3	E	6	R	L		L	F
SERIES													
NO.OF CONTACTS													
14,15,26&44													
TYPE OF CONTACTS													
S-SOCKET													
TYPE OF TERMINATION													
13-ANGLED SPILL													
PITCH 2.54 USA													
FOOT PRINT 8.89 USA													
HEIGHT OF TERMINATION													
E-2.00 PIP SOLDERING													
LEAD FREE													
SPECIAL CODE													
12-->HIGH TEMP+HEAT SEALING TAPE & REEL PACKING.													
09-->TRAY PACKING.													
132-->HIGH TEMP+PRESSURE SEALING TAPE & REEL PACKING.													
MOUNTING OPTIONS													
RL->PIP METAL PEG+INSERTM3+METAL BRACKET													
RX->PIP METAL PEG+INSERT UNC 4.40+METAL BRACKET													
RV->PIP METAL PEG+F.SCREW LOCK UNC 4.40+METAL BRACKET													
PLATING													
6: ≥500 mating/unmating													
4: ≥200 mating/unmating													


"This product meets European Union Directives and other country regulations as described in GS-47-0004"

The housing will withstand exposure to 260°C peak temperature for 30 seconds in a convection,infra-red or vapor reflow oven solder application.


Packaging as per GS-14-920

TRUE POSITION : $\phi 0.36$

SIZE	DIMENSIONS						
	A±0.38	B±0.12	C±0.10	D ^{+0.25} ₋₀	E	F	G
14/15	30.81	24.99	16.96	16.21	8.19	2.28	1.14
26	39.14	33.32	25.18	24.54	8.01	2.285	1.14
44	53.03	47.04	39.12	38.25	8.02	2.285	1.14



VIEW FOR MOUNTING OPTION - RV



PRODUCT SPECIFICATION

See :- GS-12-607

PACKAGING SPECIFICATION

See :- GS-14-1139 - Tape & Reel Packing

See :- GS-14-1157 - Tray Packing

NOTES :

- 1) GENRAL VIEW IS FOR MOUNTING OPTION - RX/RL
- 2) FOR 14 POSN , HOLE NO:9 IS BLOCKED

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family COMPACT D
ltr	ecn no	dr	date	tolerances unless otherwise specified		ϕ	title
A	I07-0166	AS	2007-12-4	angles	linear	MM	C-D A/S FEMALE PIP CONNECTOR
B	I09-0130	AS	2009-7-8				
C	I09-0202	NG	2009-9-24			scale	
D	I11-0052	RPK	2011-3-17	dr	ANISH.SALAM	2007-12-04	dwg no
E	ELX-I-21007	AB	2015/06/03	enr	ALIAS.BABU	2015/06/03	sheet 1 of 1
				chr	MITHUN.PAUL	2015/06/03	size
				appd	BIJU.K.PAUL	2015/06/03	A3
sheet	revision	E					type
index	sheet	1					Product Customer Drawing

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI / Amphenol:

<u>CD15S13E4RL09LF</u>	<u>CD15S13E4RL12LF</u>	<u>CD15S13E4RV09LF</u>	<u>CD15S13E4RV12LF</u>	<u>CD15S13E4RX09LF</u>
<u>CD15S13E6RL09LF</u>	<u>CD15S13E6RL12LF</u>	<u>CD15S13E6RV09LF</u>	<u>CD15S13E6RV12LF</u>	<u>CD15S13E6RX09LF</u>
<u>CD26S13E4RL09LF</u>	<u>CD26S13E4RL12LF</u>	<u>CD26S13E4RV09LF</u>	<u>CD26S13E4RV12LF</u>	<u>CD26S13E4RX09LF</u>
<u>CD26S13E4RX12LF</u>	<u>CD26S13E6RL09LF</u>	<u>CD26S13E6RL12LF</u>	<u>CD26S13E6RV09LF</u>	<u>CD26S13E6RV12LF</u>
<u>CD26S13E6RX09LF</u>	<u>CD26S13E6RX12LF</u>	<u>CD44S13E4RL09LF</u>	<u>CD44S13E4RL12LF</u>	<u>CD44S13E4RV09LF</u>
<u>CD44S13E4RV12LF</u>	<u>CD44S13E4RX09LF</u>	<u>CD44S13E4RX12LF</u>	<u>CD44S13E6RL09LF</u>	<u>CD44S13E6RL12LF</u>
<u>CD44S13E6RV09LF</u>	<u>CD44S13E6RV12LF</u>	<u>CD44S13E6RX09LF</u>	<u>CD44S13E6RX12LF</u>	<u>CD14S13E6RV09LF</u>
<u>CD15S13E4RX12LF</u>	<u>CD15S13E6RX12LF</u>	<u>CD15S13E4RV159LF</u>		