







REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASE	14MAY19	SULLEN	TOMMY



NOTES: UNLESS OTHERWISE SPECIFIED

- MATERIAL:
HOUSING: THERMOPLASTIC, BLACK
CONTACT: COPPER ALLOY
CONTACT PLATING: NICKEL PLATED
- MODIFICATIONS: DIODE
- SPECIFICATIONS:
3.1 DIODE P/N: MUR460G
3.2 PEAK REVERSE VOLTAGE: 600.0 V MAX.
3.3 PEAK FORWARD VOLTAGE: 1.28 V MAX.
3.4 AVERAGE FORWARD CURRENT: 4.0 A MAX.
3.5 OPERATING TEMPERATURE: -55°C TO +125°C
3.6 MOISTURE RESISTANCE: IP67
3.7 MATING CYCLE DURABILITY: 100 CYCLES
3.8 RoHS COMPLIANT
- MATING PART: AT06-4S*
(* = ALL MODIFICATIONS)
- ALL DIMENSIONS ARE FOR REFERENCE USE ONLY



AT04-4P-RT01		REF: DT04-4P-RT01		
PART NUMBER		DESCRIPTION		ITEM
QUANTITY	MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED		SIGNATURES		DATE
1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 Fractions ±1/64 Angles ±1° 3) Note reference = 		DRAWN: SULLENZHANG		19SEP18
		CHECKED: ORION LI		19SEP18
		ENGINEER:		
		APPROVAL: TOMMY XIE		19SEP18
MATERIAL SPECIFICATIONS:		CUSTOMER:		
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		
NEXT ASSY:		SIZE	TYPE	DWG NO:
		B	C-	AT04-4P-RT01
		SCALE	NONE	
		SHEET 1 OF 1		REVISION
				A1

TITLE: RECEPTACLE 4PIN, TERMINATOR, AT SERIES
DWG NO: AT04-4P-RT01
REV: A1
SH: 1
OF: 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[AT04-4P-RT01](#)