




- Feature metal pawl for high strength and better durability.
- Self-locking head design speeds installation and locks into place at any length along the tie body.
- Provide a strong, durable method of cable bundling.
- Can be used in a wide range of indoor, outdoor, and underground (including direct burial) applications.
- Smooth surfaces and rounded edges assure cable protection and worker safety.
- Part Description Key: NTMP-XXX-YYY where XXX = tensile (foot pounds) and YYY = length (inches x 10).
- These parts are not covered under Heyco's solar warranty.

Heyco® Nytyes® with Stainless Steel Locking Device

PART SPECIFICATIONS				PART NO.		DESCRIPTION	PART DIMENSIONS					
Min. Tensile Strength		Max. Bundle Diameter		Natural	Black		A Length		B Width		C Thickness	
Lbs.	N	in.	mm.				in.	mm.	in.	mm.	in.	mm.
18	80	.87	22,0	13000	13000B	NTMP-018-039	3.90	100	.12	3,0	.04	1,1
35	160	1.42	36,0	13001	13001B	NTMP-036-059	5.90	150	.16	4,0	.05	1,2
		2.09	53,0	13002	13002B	NTMP-036-079	7.90	200				
45	200	2.56	65,0	13003	13003B	NTMP-045-098	9.80	250	.20	5,0	.06	1,5
		2.99	76,0	13004	13004B	NTMP-045-118	11.80	300				
56	250	2.09	53,0	13008	13008B	NTMP-056-079	7.90	200	.31	8,0		
		2.60	66,0	13009	13009B	NTMP-056-094	9.40	240				
		2.99	76,0	13010	13010B	NTMP-056-118	11.80	300				
112	500	2.99	76,0	13011	13011B	NTMP-112-118	11.80	300	.39	10,0	.07	1,7
		3.74	95,0	13012	13012B	NTMP-112-138	13.80	350				
		4.45	113,0	13013	13013B	NTMP-112-157	15.70	400				
124	550	4.72	120,0	13014	13014B	NTMP-124-177	17.70	450				
		6.22	158,0	13015	13015B	NTMP-124-197	19.70	500				

Standard colors natural and UV Black.



Material: Nylon 6/6 wire tie with a stainless steel locking pawl
 Flammability Rating: 94V-2
 Temperature Range: -40°F (-40°C) to 185°F (85°C)



- **Extremely durable, vinyl jacketed Stainless Steel Cable Tie.**
- Smooth vinyl jacketing prevents damage to installation cable insulation.
- Stainless steel crimp sleeve for easy field installation with electrician linesman pliers, or wire cutters.
- **Certified by UL Specification 62275 for indoor and outdoor usage.**
- UV protected vinyl jacket is excellent for solar installation where product durability is required.
- Use standard wire cutters to both crimp the sleeve and cut the excess wire.
- Not for use in a marine salt water environment. Contact Heyco for alternative materials.
- DFARS Compliant.


Heyco® SunBundler®

Crimp Lock PVC Coated Stainless Steel Wire Cable Ties



PART SPECIFICATIONS				PART NO.		DESCRIPTION	PART DIMENSIONS			
Max. Tensile Strength		Max. Bundle Diameter		100 Pack	Bulk		A Length		B Diameter	
Lbs.	N	in.	mm.				in.	mm.	in.	mm.
Black vinyl jacketed 302/304 stainless steel wire										
100	440	2.30	58,4	S6408	S6409	SunBundler® 8	8	203	.06	1,6
		2.92	74,2	S6410	S6411	SunBundler® 10	10	254		
		3.88	98,6	S6412	S6413	SunBundler® 12	12	305		
		4.20	106,7	S6414	S6415	SunBundler® 14	14	356		
		6.36	161,5	S6420	S6421	SunBundler® 20	20	508		

Standard color Black.



Material: Commercial Aircraft Grade 302/304 stainless wire w/UV protected vinyl jacket
 Certifications: Certified by Underwriters' Laboratories for Compliance to both Canadian and U.S. Requirements under File E54523
 Temperature Range: -40°F (-40°C) to 221°F (105°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[13002B](#) [13000B](#) [13015](#) [13001B](#) [13003](#) [13011](#) [13011B](#) [13013B](#) [13008B](#) [13004](#) [13000](#) [13009](#) [13009B](#) [13004B](#)
[13014](#) [13002](#) [13015B](#) [13008](#) [13010B](#) [13013](#) [13012B](#) [13014B](#) [13001](#) [13012](#) [13010](#) [13003B](#) [13003B-P](#)