




Heyco® Nylon PCB Supports - Imperial Spacing



	Maximum Thickness		Mounting Hole Diameter		Maximum Thickness		Mounting Hole Diameter		Maximum Thickness		Mounting Hole Diameter		Maximum Thickness		Mounting Hole Diameter	
	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
PCB	.078	2,0	.125	3,2	.078	2,0	.157	4,0	.078	2,0	.187	4,8	.078	2,0	.157	4,0
Chassis	.078	2,0	.125	3,2	.078	2,0	.157	4,0	.078	2,0	.187	4,8	.078	2,0	.187	4,8
A			PART NO.	DESCRIPTION	PART NO.	DESCRIPTION	PART NO.	DESCRIPTION	PART NO.	DESCRIPTION	PART NO.	DESCRIPTION	PART NO.	DESCRIPTION	PART NO.	DESCRIPTION
in.	mm.	Natural			Natural				Natural				Natural			
.187	4,8	10199		HDLSP4-03	10209		HDLSP5-03	10217	HDLSP6-03		10225	HDLSP7-03				
.250	6,4	10200		HDLSP4-04	10210		HDLSP5-04	10218	HDLSP6-04		10226	HDLSP7-04				
.312	7,9	10201		HDLSP4-05												
.375	9,5	10202		HDLSP4-06	10211		HDLSP5-06	10219	HDLSP6-06		10227	HDLSP7-06				
.437	11,1	10203		HDLSP4-07												
.500	12,7	10204		HDLSP4-08	10212		HDLSP5-08	10220	HDLSP6-08		10228	HDLSP7-08				
.562	14,3	10205		HDLSP4-09												
.625	15,9	10206		HDLSP4-10	10213		HDLSP5-10	10221	HDLSP6-10		10229	HDLSP7-10				
.750	19,1				10214		HDLSP5-12	10222	HDLSP6-12		10230	HDLSP7-12				
.875	22,2	10207		HDLSP4-14	10215		HDLSP5-14	10223	HDLSP6-14		10231	HDLSP7-14				

Standard color natural. For special order parts in UL 94V-0 natural material, add the suffix "F" to Part No.

Quick
Specs

Material: Nylon 6/6
Flammability Rating: 94V-2
Temperature Range: .4°F (-18°C) to 185°F (85°C)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[10221F](#) [10220F](#) [10203F](#) [10201F](#) [10222F](#) [10218F](#) [10211F](#) [10217F](#) [10202F](#) [10215F](#) [10209F](#) [10206F](#) [10219F](#)
[10226F](#) [10199F](#) [10227F](#) [10214F](#) [10204F](#) [10229F](#) [10207F](#) [10230F](#) [10225F](#) [10205F](#) [10228F](#) [10231F](#) [10223F](#)
[10200F](#) [10210F](#) [10212F](#) [10213F](#) [10216F](#)