





## Heyco® Nylon PCB Supports - Imperial Spacing




FLANGED TWO PRONG SNAP FIT /  
FLANGED TWO PRONG SNAP LOCK

### HMSPS




FLAT TOP REST MOUNT /  
ARROWHEAD LOCK

### HMPS



FLAT TOP REST MOUNT /  
TEARDROP SNAP LOCK

### HPS-TD



TEARDROP SNAP LOCK /  
TEARDROP SNAP LOCK

### HSP-MDL-3

|         |      | Maximum Thickness |     | Mounting Hole Diameter |     | Maximum Thickness   |     | Mounting Hole Diameter |     | Maximum Thickness   |     | Mounting Hole Diameter |     | Maximum Thickness |     | Mounting Hole Diameter |     |
|---------|------|-------------------|-----|------------------------|-----|---------------------|-----|------------------------|-----|---------------------|-----|------------------------|-----|-------------------|-----|------------------------|-----|
|         |      | in.               | mm. | in.                    | mm. | in.                 | mm. | in.                    | mm. | in.                 | mm. | in.                    | mm. | in.               | mm. | in.                    | mm. |
| PCB     |      | .062              | 1,6 | .157                   | 4,0 | flat top rest mount |     |                        |     | flat top rest mount |     |                        |     | .062              | 1,6 | .098                   | 2,5 |
| Chassis |      | .062              | 1,6 | .157                   | 4,0 | .078                | 2,0 | .125                   | 3,2 | .062                | 1,6 | .098                   | 2,5 | .039              | 1,0 | .078                   | 2,0 |
| A       |      | PART NO.          |     | DESCRIPTION            |     | PART NO.            |     | DESCRIPTION            |     | PART NO.            |     | DESCRIPTION            |     | PART NO.          |     | DESCRIPTION            |     |
| in.     | mm.  | Natural           |     |                        |     | Natural             |     |                        |     | Natural             |     |                        |     | Natural           |     |                        |     |
| .063    | 1,6  |                   |     |                        |     |                     |     |                        |     | 10341               |     | HPS-TD-01              |     | 10352             |     | HSP-MDL-3-01           |     |
| .125    | 3,2  |                   |     |                        |     | 10331               |     | HMPS-02                |     | 10342               |     | HPS-TD-02              |     | 10353             |     | HSP-MDL-3-02           |     |
| .187    | 4,8  | 10320             |     | HMSPS-03               |     | 10332               |     | HMPS-03                |     | 10343               |     | HPS-TD-03              |     | 10354             |     | HSP-MDL-3-03           |     |
| .250    | 6,4  | 10321             |     | HMSPS-04               |     | 10333               |     | HMPS-04                |     | 10344               |     | HPS-TD-04              |     | 10355             |     | HSP-MDL-3-04           |     |
| .312    | 7,9  | 10322             |     | HMSPS-05               |     | 10334               |     | HMPS-05                |     | 10345               |     | HPS-TD-05              |     | 10356             |     | HSP-MDL-3-05           |     |
| .375    | 9,5  | 10323             |     | HMSPS-06               |     | 10335               |     | HMPS-06                |     | 10346               |     | HPS-TD-06              |     | 10357             |     | HSP-MDL-3-06           |     |
| .437    | 11,1 | 10324             |     | HMSPS-07               |     | 10336               |     | HMPS-07                |     | 10347               |     | HPS-TD-07              |     |                   |     |                        |     |
| .500    | 12,7 | 10325             |     | HMSPS-08               |     | 10337               |     | HMPS-08                |     | 10348               |     | HPS-TD-08              |     |                   |     |                        |     |
| .562    | 14,3 |                   |     |                        |     | 10338               |     | HMPS-09                |     | 10349               |     | HPS-TD-09              |     |                   |     |                        |     |
| .625    | 15,9 | 10326             |     | HMSPS-10               |     | 10339               |     | HMPS-10                |     | 10350               |     | HPS-TD-10              |     |                   |     |                        |     |
| .689    | 17,5 | 10327             |     | HMSPS-11               |     |                     |     |                        |     |                     |     |                        |     |                   |     |                        |     |
| .750    | 19,1 | 10328             |     | HMSPS-12               |     |                     |     |                        |     |                     |     |                        |     |                   |     |                        |     |
| .875    | 22,2 | 10329             |     | HMSPS-14               |     |                     |     |                        |     |                     |     |                        |     |                   |     |                        |     |

Standard color natural. For special order parts in UL 94V-0 natural material, add the suffix “F” to Part No.

Material: Nylon 6/6  
Flammability Rating: 94V-2  
Temperature Range: .4°F (-18°C) to 185°F (85°C)

*Quick  
Specs*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[10344F](#) [10345F](#) [10350F](#) [10337F](#) [10323F](#) [10320F](#) [10321F](#) [10355F](#) [10339F](#) [10324F](#) [10336F](#) [10354F](#) [10352F](#)  
[10356F](#) [10332F](#) [10357F](#) [10333F](#) [10322F](#) [10331F](#) [10329F](#) [10328F](#) [10334F](#) [10325F](#) [10335F](#) [10353F](#) [10346F](#)  
[10326F](#) [10341F](#) [10338F](#) [10348F](#) [10347F](#) [10349F](#) [10343F](#) [10342F](#) [10327F](#)