







## Heyco® Nylon PCB Supports - Metric Spacing

|                                                                                                                                                              |                                                                                                                                                              |                                                                                                                                                                |                                                                                                                                                                 |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TEARDROP SNAP LOCK /<br/>TEARDROP SNAP LOCK</p> <p><b>HSP-MDL-1</b></p> |  <p>TEARDROP SNAP LOCK /<br/>TEARDROP SNAP LOCK</p> <p><b>HSP-MDL-2</b></p> |  <p>TEARDROP SNAP LOCK /<br/>TEARDROP SNAP LOCK</p> <p><b>HSP-MDLS-1</b></p> |  <p>TEARDROP SNAP LOCK /<br/>TEARDROP SNAP LOCK</p> <p><b>HSP-MDLS-2</b></p> |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|

|         | Maximum Thickness |     | Mounting Hole Diameter |     | Maximum Thickness |     | Mounting Hole Diameter |     | Maximum Thickness |     | Mounting Hole Diameter |     | Maximum Thickness |     | Mounting Hole Diameter |     |
|---------|-------------------|-----|------------------------|-----|-------------------|-----|------------------------|-----|-------------------|-----|------------------------|-----|-------------------|-----|------------------------|-----|
| PCB     | .062              | 1,6 | .098                   | 2,5 | .062              | 1,6 | .137                   | 3,5 | .062              | 1,6 | .098                   | 2,5 | .062              | 1,6 | .137                   | 3,5 |
| Chassis | .062              | 1,6 | .098                   | 2,5 | .062              | 1,6 | .137                   | 3,5 | .141              | 3,6 | .098                   | 2,5 | .141              | 3,6 | .137                   | 3,5 |

| A<br>mm. | PART NO.<br>Natural | DESCRIPTION     | PART NO.<br>Natural | DESCRIPTION     | PART NO.<br>Natural | DESCRIPTION    | PART NO.<br>Natural | DESCRIPTION    |
|----------|---------------------|-----------------|---------------------|-----------------|---------------------|----------------|---------------------|----------------|
| 2,0      | <b>10444</b>        | HSP-MDL-1-02M   | <b>10461</b>        | HSP-MDL-2-02M   | <b>10478</b>        | HSP-MDLS-1-02M | <b>10493</b>        | HSP-MDLS-2-02M |
| 3,0      | <b>10445</b>        | HSP-MDL-1-03M   | <b>10462</b>        | HSP-MDL-2-03M   | <b>10479</b>        | HSP-MDLS-1-03M | <b>10494</b>        | HSP-MDLS-2-03M |
| 4,0      | <b>10446</b>        | HSP-MDL-1-04M   | <b>10463</b>        | HSP-MDL-2-04M   | <b>10480</b>        | HSP-MDLS-1-04M | <b>10495</b>        | HSP-MDLS-2-04M |
| 5,0      | <b>10447</b>        | HSP-MDL-1-05M   | <b>10464</b>        | HSP-MDL-2-05M   | <b>10481</b>        | HSP-MDLS-1-05M | <b>10496</b>        | HSP-MDLS-2-05M |
| 6,0      | <b>10448</b>        | HSP-MDL-1-06M   | <b>10465</b>        | HSP-MDL-2-06M   | <b>10482</b>        | HSP-MDLS-1-06M | <b>10497</b>        | HSP-MDLS-2-06M |
| 7,0      | <b>10449</b>        | HSP-MDL-1-07M   | <b>10466</b>        | HSP-MDL-2-07M   | <b>10483</b>        | HSP-MDLS-1-07M | <b>10498</b>        | HSP-MDLS-2-07M |
| 8,0      | <b>10450</b>        | HSP-MDL-1-08M   | <b>10467</b>        | HSP-MDL-2-08M   | <b>10484</b>        | HSP-MDLS-1-08M | <b>10499</b>        | HSP-MDLS-2-08M |
| 9,0      | <b>10451</b>        | HSP-MDL-1-09M   | <b>10468</b>        | HSP-MDL-2-09M   |                     |                |                     |                |
| 10,0     | <b>10452</b>        | HSP-MDL-1-10M   | <b>10469</b>        | HSP-MDL-2-10M   | <b>10485</b>        | HSP-MDLS-1-10M | <b>10500</b>        | HSP-MDLS-2-10M |
| 12,0     | <b>10453</b>        | HSP-MDL-1-12M   | <b>10470</b>        | HSP-MDL-2-12M   | <b>10486</b>        | HSP-MDLS-1-12M | <b>10501</b>        | HSP-MDLS-2-12M |
| 14,0     | <b>10454</b>        | HSP-MDL-1-14M   | <b>10471</b>        | HSP-MDL-2-14M   | <b>10487</b>        | HSP-MDLS-1-14M | <b>10502</b>        | HSP-MDLS-2-14M |
| 16,0     | <b>10455</b>        | HSP-MDL-1-16M   | <b>10472</b>        | HSP-MDL-2-16M   | <b>10488</b>        | HSP-MDLS-1-16M | <b>10503</b>        | HSP-MDLS-2-16M |
| 18,0     | <b>10456</b>        | HSP-MDL-1-18M   | <b>10473</b>        | HSP-MDL-2-18M   | <b>10489</b>        | HSP-MDLS-1-18M | <b>10504</b>        | HSP-MDLS-2-18M |
| 20,0     | <b>10457</b>        | HSP-MDL-1-20M   | <b>10474</b>        | HSP-MDL-2-20M   | <b>10490</b>        | HSP-MDLS-1-20M | <b>10505</b>        | HSP-MDLS-2-20M |
| 22,0     | <b>10458</b>        | HSP-MDL-1-22M   | <b>10475</b>        | HSP-MDL-2-22M   | <b>10491</b>        | HSP-MDLS-1-22M | <b>10506</b>        | HSP-MDLS-2-22M |
| 26,5     | <b>10459</b>        | HSP-MDL-1-26.5M | <b>10476</b>        | HSP-MDL-2-26.5M |                     |                |                     |                |

Standard color natural. For special order parts in UL 94V-0 natural material, add the suffix "F" to Part No.

*Quick  
Specs*

Material Nylon 6/6  
Flammability Rating 94V-2  
Temperature Range .4°F (-18°C) to 185°F (85°C)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Heyco:

|                               |                               |                               |                               |                               |                               |                               |                               |                               |                               |                               |                               |                               |
|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|
| <a href="#"><u>10502F</u></a> | <a href="#"><u>10506F</u></a> | <a href="#"><u>10474F</u></a> | <a href="#"><u>10494F</u></a> | <a href="#"><u>10478F</u></a> | <a href="#"><u>10483F</u></a> | <a href="#"><u>10496F</u></a> | <a href="#"><u>10497F</u></a> | <a href="#"><u>10489F</u></a> | <a href="#"><u>10501F</u></a> | <a href="#"><u>10471F</u></a> | <a href="#"><u>10466F</u></a> | <a href="#"><u>10444F</u></a> |
| <a href="#"><u>10505F</u></a> | <a href="#"><u>10456F</u></a> | <a href="#"><u>10479F</u></a> | <a href="#"><u>10481F</u></a> | <a href="#"><u>10461F</u></a> | <a href="#"><u>10445F</u></a> | <a href="#"><u>10468F</u></a> | <a href="#"><u>10449F</u></a> | <a href="#"><u>10465F</u></a> | <a href="#"><u>10446F</u></a> | <a href="#"><u>10464F</u></a> | <a href="#"><u>10500F</u></a> | <a href="#"><u>10452F</u></a> |
| <a href="#"><u>10490F</u></a> | <a href="#"><u>10475F</u></a> | <a href="#"><u>10459F</u></a> | <a href="#"><u>10447F</u></a> | <a href="#"><u>10484F</u></a> | <a href="#"><u>10448F</u></a> | <a href="#"><u>10463F</u></a> | <a href="#"><u>10467F</u></a> | <a href="#"><u>10486F</u></a> | <a href="#"><u>10488F</u></a> | <a href="#"><u>10453F</u></a> | <a href="#"><u>10457F</u></a> | <a href="#"><u>10458F</u></a> |
| <a href="#"><u>10498F</u></a> | <a href="#"><u>10504F</u></a> | <a href="#"><u>10493F</u></a> | <a href="#"><u>10499F</u></a> | <a href="#"><u>10454F</u></a> | <a href="#"><u>10470F</u></a> | <a href="#"><u>10491F</u></a> | <a href="#"><u>10476F</u></a> | <a href="#"><u>10472F</u></a> | <a href="#"><u>10473F</u></a> | <a href="#"><u>10485F</u></a> | <a href="#"><u>10480F</u></a> | <a href="#"><u>10482F</u></a> |
| <a href="#"><u>10495F</u></a> | <a href="#"><u>10455F</u></a> | <a href="#"><u>10469F</u></a> | <a href="#"><u>10450F</u></a> | <a href="#"><u>10503F</u></a> | <a href="#"><u>10487F</u></a> | <a href="#"><u>10462F</u></a> | <a href="#"><u>10451F</u></a> |                               |                               |                               |                               |                               |