

"Stay Connected" with



HEYware Products

a PennEngineering® Company



Heyco® Hook and Loop – Ties

PART NO.								DESCRIPTION	PART DIMENSIONS			
Black	White	Gray	Orange	Yellow	Red	Blue	Green		A		B	
									Length		Width	
									in.	mm.	in.	mm.
16005	16006	16007	16008	16009	16010	16011	16012	HLT-1/2-6	6.0	152	0.50	12,7
16021	16022	16023	16024	16025	16026	16027	16028	HLT-1/2-8	8.0	203		
16037	16038	16039	16040	16041	16042	16043	16044	HLT-1/2-10	10.0	254		
16053	16054	16055	16056	16057	16058	16059	16060	HLT-1/2-12	12.0	305		
16069	16070	16071	16072	16073	16074	16075	16076	HLT-3/4-6	6.0	152	0.75	19
16085	16086	16087	16088	16089	16090	16091	16092	HLT-3/4-8	8.0	203		
16101	16102	16103	16104	16105	16106	16107	16108	HLT-3/4-10	10.0	254		
16117	16118	16119	16120	16121	16122	16123	16124	HLT-3/4-12	12.0	305		
16133	16134	16135	16136	16137	16138	16139	16140	HLT-3/4-15	15.0	381		
16149	16150	16151	16152	16153	16154	16155	16156	HLT-3/4-18	18.0	457		
16165	16166	16167	16168	16169	16170	16171	16172	HLT-3/4-24	24.0	610		



Heyco® Hook and Loop – Cinch Ties

PART NO.								DESCRIPTION	PART DIMENSIONS			
Black	White	Gray	Orange	Yellow	Red	Blue	Green		A		B	
									Length		Width	
								in.	mm.			
16190	16191	16192	16193	16194	16195	16196	16197	HLCT-3/4-6	6.0	152	0.75	19
16206	16207	16208	16209	16210	16211	16212	16213	HLCT-3/4-12	12.0	305		
16222	16223	16224	16225	16226	16227	16228	16229	HLCT-3/4-18	18.0	457		
16238	16239	16240	16241	16242	16243	16244	16245	HLCT-1-9	9.0	229	0.98	25
16254	16255	16256	16257	16258	16259	16260	16261	HLCT-1-12	12.0	305		
16270	16271	16272	16273	16274	16275	16276	16277	HLCT-1-15	15.0	381		
16286	16287	16288	16289	16290	16291	16292	16293	HLCT-1-20	20.0	508		
16302	16303	16304	16305	16306	16307	16308	16309	HLCT-1-1/2-11	11.0	280	1.50	38
16318	16319	16320	16321	16322	16323	16324	16325	HLCT-2-15	15.0	381	1.97	50

- Reusable
- Easy application and bundle of cables
- Cinch Straps offer light axial retention

*Quick
Specs*

Material Nylon
Peel Durability >5000 Cycles
Temperature Range -4°F (-20°C) to 176°F (80°C)

"Stay Connected" with



HEYware Products


a PennEngineering® Company




Heyco® Hook and Loop – Rolls

PART NO.								DESCRIPTION	PART DIMENSIONS			
Black	White	Gray	Orange	Yellow	Red	Blue	Green		A		B	
									Length		Width	
								m	m	in.	mm.	
16343	16344	16345	16346	16347	16348	16349	16350	HLR-1/2-5	16.4	5	0.51	13
16359	16360	16361	16362	16363	16364	16365	16366	HLR-3/4-5	16.4	5	0.75	19
16375	16376	16377	16378	16379	16380	16381	16382	HLR-1-5	16.4	5	0.98	25
16391	16392	16393	16394	16395	16396	16397	16398	HLR-1/2-10	32.8	10	0.51	13
16407	16408	16409	16410	16411	16412	16413	16414	HLR-3/4-10	32.8	10	0.75	19
16423	16424	16425	16426	16427	16428	16429	16430	HLR-1-10	32.8	10	0.98	25


- Reusable
- Easy application and bundle of cables
- Rolls can be cut to length offering flexibility on job site/application



HLT – Ties



HLCT – Cinch Ties



HLR – Rolls

Material	Nylon
Peel Durability	>5000 Cycles
Temperature Range	-4°F (-20°C) to 176°F (80°C)

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

<u>16005</u>	<u>16006</u>	<u>16007</u>	<u>16008</u>	<u>16009</u>	<u>16010</u>	<u>16011</u>	<u>16012</u>	<u>16021</u>	<u>16022</u>	<u>16023</u>	<u>16024</u>	<u>16025</u>	<u>16026</u>	<u>16027</u>
<u>16028</u>	<u>16037</u>	<u>16038</u>	<u>16039</u>	<u>16040</u>	<u>16041</u>	<u>16042</u>	<u>16043</u>	<u>16044</u>	<u>16053</u>	<u>16054</u>	<u>16055</u>	<u>16056</u>	<u>16057</u>	<u>16058</u>
<u>16059</u>	<u>16060</u>	<u>16069</u>	<u>16070</u>	<u>16071</u>	<u>16072</u>	<u>16073</u>	<u>16074</u>	<u>16075</u>	<u>16076</u>	<u>16085</u>	<u>16086</u>	<u>16087</u>	<u>16088</u>	<u>16089</u>
<u>16090</u>	<u>16091</u>	<u>16092</u>	<u>16101</u>	<u>16102</u>	<u>16103</u>	<u>16104</u>	<u>16105</u>	<u>16106</u>	<u>16107</u>	<u>16108</u>	<u>16117</u>	<u>16118</u>	<u>16119</u>	<u>16120</u>
<u>16121</u>	<u>16122</u>	<u>16123</u>	<u>16124</u>	<u>16133</u>	<u>16134</u>	<u>16135</u>	<u>16136</u>	<u>16137</u>	<u>16138</u>	<u>16139</u>	<u>16140</u>	<u>16149</u>	<u>16150</u>	<u>16151</u>
<u>16152</u>	<u>16153</u>	<u>16154</u>	<u>16155</u>	<u>16156</u>	<u>16165</u>	<u>16166</u>	<u>16167</u>	<u>16168</u>	<u>16169</u>	<u>16170</u>	<u>16171</u>	<u>16172</u>	<u>16190</u>	<u>16191</u>
<u>16192</u>	<u>16193</u>	<u>16194</u>	<u>16195</u>	<u>16196</u>	<u>16197</u>	<u>16206</u>	<u>16207</u>	<u>16208</u>	<u>16209</u>					