





- NOTE) 1 . ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX
2 . CONTACT PLATING SPECIFICATIONS
CONTACT AREA : GOLD 0.05 μ m MIN
SMT LEAD : GOLD 0.05 μ m MIN
UNDERPLATING : NICKEL 1 μ m MIN
(SURFACE : SEALING)
3 . HRS MARK AND CAV No. ARE INDICATED IN APPROX POSITION SHOWN.
4 . A PART OF THE WALL COULD BE NOTCHED.



A-A (50:1)




ENGAGEMENT FIGURE (50:1)



3	PS	CLEAR (ENBOSSED CARRIER TAPE)	6	PS	CLEAR (REINFORCEMENT COLLAR)
2	PHOSPHOR BRONZE	2	5	PS	BLACK (PLASTIC REEL)
1	LCP	UL94 V-0, BLACK	4	POLYESTER	CLEAR (COVER TAPE)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 10 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED
HIROSE ELECTRIC CO., LTD.		APPROVED : MO. ISHIDA	16. 04. 26	DRAWING NO.	EDC-324415-51-00
		CHECKED : TS. MIYAZAKI	16. 04. 26	PART NO.	BM14C(0.8)-14DP-0.4V(51)
		DESIGNED : NY. YAMASHIRO	16. 04. 26	CODE NO.	CL684-8025-8-51
		DRAWN : SN. NUMAZAKI	16. 04. 25		
					1/3


Aug.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

◆ RECOMMENDED PCB LAYOUT




◆ RECOMMENDED METAL MASK DIMENSIONS


METAL MASK THICKNESS : $100 \mu\text{m}$



METAL MASK THICKNESS : $120 \mu\text{m}$



6 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.



REFLOW METHOD: IR REFLOW

NUMBER OF REFLOW CYCLES: 2 CYCLES MAX.

1) REFLOW TIME

DURATION ABOVE 220°C: 60 SEC. MAX.
(PEAK TEMPERATURE: 250°C MAX)

2) PRE-HEAT TIME

PRE-HEAT TEMPERATURE(MIN): 150°C
PRE-HEAT TEMPERATURE(MAX): 180°C
PRE-HEAT TIME: 90-120 sec.


6 THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE.
ADDITIONAL FACTORS, SUCH AS SOLDER PASTE TYPE, PCB SIZE AND
OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE, THEREFORE,
A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED
PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.

HRS

DRAWING NO.	EDC-324415-51-00
PART NO.	BM14C(0.8)-14DP-0.4V(51)
CODE NO.	CL684-8025-8-51

2/3

Aug.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



HRS	DRAWING NO.	EDC-324415-51-00		
	PART NO.	BM14C(0.8)-14DP-0.4V(51)		
	CODE NO.	CL684-8025-8-51	$\triangle$	$\frac{3}{3}$

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[BM14C\(0.8\)-14DP-0.4V\(51\)](#)