





A-A(FREE)



ENGAGEMENT FIGURE (FREE)


BM14B(0.8)-40DP-0.4V(\*\*)




BM14EB(1.3)-40DS-0.4V(51)

- NOTE) 1 . ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX  
2 . EACH CONTACTS AT 4 CORNERS ARE PROVIDED FOR METAL FITTINGS AND GROUNDING PURPOSE.  
3 . HRS MARK AND CAV NO. ARE INDICATED IN APPROX POSITION SHOWN.  
4 . GATE POSITION IS INDICATED IN APPROX POSITION SHOWN.

|     |                 |                                  |     |           |                               |
|-----|-----------------|----------------------------------|-----|-----------|-------------------------------|
| 2   | PHOSPHOR BRONZE | CONTACT AREA : GOLD 0.05 μm MIN. | 6   | PS        | CLEAR (REINFORCEMENT COLLAR)  |
|     |                 | SMT LEAD : GOLD 0.05 μm MIN.     | 5   | PS        | BLACK (PLASTIC REEL)          |
|     |                 | UNDERPLATING : NICKEL 1 μm MIN.  | 4   | POLYESTER | CLEAR (COVER TAPE)            |
| 1   | LCP             | UL94 V-0, BLACK                  | 3   | PS        | CLEAR (ENBOSSED CARRIER TAPE) |
| NO. | MATERIAL        | FINISH , REMARKS                 | NO. | MATERIAL  | FINISH , REMARKS              |


|                                                                                                                 |                                                                                       |                       |                                                                                       |                                                                                           |                           |          |         |      |
|-----------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-----------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|---------------------------|----------|---------|------|
| UNITS<br>mm                                                                                                     |  | SCALE<br>10 : 1       |  | COUNT                                                                                     | DESCRIPTION OF REVISIONS  | DESIGNED | CHECKED | DATE |
|  HIROSE ELECTRIC CO., LTD. |                                                                                       | APPROVED : KH. IKEDA  | 14. 02. 24                                                                            | DRAWING NO.                                                                               | EDC3-341489-01            |          |         |      |
|                                                                                                                 |                                                                                       | CHECKED : YH. MICHIDA | 14. 02. 24                                                                            | PART NO.                                                                                  | BM14EB(1.3)-40DS-0.4V(51) |          |         |      |
|                                                                                                                 |                                                                                       | DESIGNED : SH. HOSODA | 14. 02. 21                                                                            | CODE NO.                                                                                  | CL684-8174-8-51           |          |         |      |
|                                                                                                                 |                                                                                       | DRAWN : SH. HOSODA    | 14. 02. 21                                                                            |  1/3 |                           |          |         |      |

◆ RECOMMENDED PCB LAYOUT




◆ RECOMMENDED METAL MASK DIMENSIONS

METAL MASK THICKNESS :  $100 \mu\text{m}$



5 RECOMMENDED REFLOW TEMPERATURE PROFILE USING LEAD-FREE SOLDER PASTE.



REFLOW METHOD: IR REFLOW  
NUMBER OF REFLOW CYCLES: 2 CYCLES MAX.

- 1) REFLOW TIME  
DURATION ABOVE 220°C, 60 SEC. MAX.  
(PEAK TEMPERATURE: 250°C MAX)
- 2) PRE-HEAT TIME  
PRE-HEAT TEMPERATURE(MIN): 150°C  
PRE-HEAT TEMPERATURE(MAX): 180°C  
PRE-HEAT TIME: 90-120 sec.


5 THIS TEMPERATURE PROFILE IS PER THE CONDITIONS SHOWN ABOVE.  
ADDITIONAL FACTORS, SUCH AS SOLDER PASTE TYPE, PCB SIZE AND  
OTHER MOUNTED COMPONENTS COULD AFFECT THE PROFILE, THEREFORE,  
A THOROUGH EVALUATION OF MOUNTING CONDITION IS REQUIRED  
PRIOR TO PRODUCTION. TEMPERATURE IS MEASURED AT CONTACT LEAD.

**HRS**

図番: EDC3-341489-01  
製品名: BM14EB(1.3)-40DS-0.4V(51)  
製品コード: CL684-8174-8-51

2/3

Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[BM14EB\(1.3\)-40DS-0.4V\(51\)](#)