

SIGN	DATE	DESCRIPTION	APPROVER
△	12/03'13	Update the drawing	Jacky
△	04/08'14	change the product number	Jacky
△	11/14'14	change the product description	Airy min
△	1/12'16	Add the safety certification icon and update drawing	Chenhao
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item ① Terminal body: PA66 (UL94V-0)
- Item ② Terminal: PhBz, Tin plated.
- Item ③ Terminal cover: PA66 (UL94V-0) White

Electrical

cULus

- Voltage rating: 150V
- Current rating: 7A
- Wire range:
 - Solid wire(AWG): 18-22
 - Wire strip length: 5-6mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C

△ Safety approval:

△ Staying power between the under bodysand the above body:8kgf.cm

△ Staying power between the body and the cover:2.5kgf.cm




Critical dimension: ▽



ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NS 5.75 series 2P stackable type(with hole)△						
PART NO.	NS0200C00010G/AG △			DWG NO.	BNS0006		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Chenhao 2016.1.12	Chenhao 2016.1.12		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
					SHEET: 01/01	REV: F	X.XX ±0.10

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[NS0200C0001AG](#)