




This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AFCL. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AFCL. © 2016 AFCL

Amphenol
FCI


AFCL CONFIDENTIAL

PLUG KIT PART NUMBER
10149875-10XLF

OCTIS SFP/SFP+ PLUG KIT-STANDARD LEVER,PITCH 26MM





PACKING CONFIGURATION



SL NO.	COMPONENT	MATERIAL	REMARKS
1	PLUG CAP	PBT GF	-
2	HOLDER SUBSET KIT	ZAMAK+ STAINLESS STEEL+ SILICONE	PASSIVATED
3	HOUSING SUBSET KIT	PBT GF+IXEF	STANDARD FITTED LEVER
4	SPLIT RUBBER GLAND	SILICONE	-
5	TIGHTENING CONE	PA	-
6	GLAND NUT	PBT GF	COLOUR BLUE

PART NUMBER	NO: OF RUBBER GLAND	GLAND SIZE
10149875-101LF	1	Ø 6MM
10149875-102LF	3	Ø 6MM, Ø 7MM AND Ø 8MM

* OPTIONAL RUBBER GLAND DIA OF 9MM,10MM & 11.5 MM AVAILABLE ON REQUEST




TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	material	-	dr	BONEY THOMAS	11-15-2018			size	A3	scale	3:10
linear	X.	±-		ISO 406	mat code	-	eng	BONEY THOMAS			11-15-2018	ecn no	-	
	0.X	±0.3	ISO 1101	heattreat	-	chr	S.ALOSIUS	11-15-2018			rel level			In Work
	0.XX	±0.13	surface	plating/finish	-	appr	BIJU K PAUL	11-15-2018	product family		OCTIS	rev	2	
	0.XXX	±0.05		spec ref	Amphenol FCI		title	OCTIS PLUG KIT SFP/SFP+	dwg no		10149875			
	0.XXXX	±-		model name	10149875-101LF	OCTIS PLUG KIT, PITCH 26 MM								
angular	0°	±2°	ISO 1302	model revision	1			cat. no.	-	Product - Customer Drw		sheet 1 of 3		

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of AFCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of AFCI. © 2016 AFCI

Amphenol
FCi

AFCI CONFIDENTIAL


BOARD CONNECTOR WITH BULK HEAD (RECEPTACLE) DETAILS



- NOTES:
1. BOARD CONNECTOR SHOWN IS FOR REFERENCE PURPOSE. REFER DRAWING P-UE76-A20-X00XX FOR BOARD CONNECTOR DETAILS
 2. REFER DRAWING 10133694 FOR CAGE DETAILS
 3. REFER DRAWING 10138458 FOR BULK HEAD (RECEPTACLE) DETAILS
 4. SCREWS TO BE USED ARE M3 X 6MM; MATERIAL-STAINLESS STEEL
 5. CASTED MOUNTING PANEL SHOULD HAVE ON ITS REAR SIDE AN INTEGRAL RECTANGULAR REINFORCED RIBS OF 3MM THICKNESS AND 4MM WIDTH ALONG THE MOUNTING SCREW PLANE AT THE TOP AND BOTTOM TO ACCOMODATE THE BLIND INTERNAL SCREW THREAD



TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	material	-	dr	BONEY THOMAS	11-15-2018	projection	mm	size	A3	scale	3:10	
				mat code	-	eng	BONEY THOMAS	11-15-2018			ecn no	-			
linear	X.	±-	ISO 406	heattreat	-	chr	S.ALOSIUS	11-15-2018			rel level				In Work
	0.X	±0.3	ISO 1101	plating/finish	-	appr	BIJU K PAUL	11-15-2018			product family				OCTIS
	0.XX	±0.13	surface	spec ref	model name	10149875-101LF	Amphenol FCI	title			OCTIS PLUG KIT SFP/SFP+	dwg no	10149875	rev	2
	0.XXX	±0.05													
	0.XXXX	±-													
angular	0°	±2°	ISO 1302	model revision	1		cat. no.	-	Product - Customer Drw			sheet 2 of 3			

FAN-OUT DEFINITION



ØD*	RECOMMENDED GLAND SIZE
From 4.8 min to 5.8 Max	"6"
From 5.8 min to 6.8 Max	"7"
From 6.8 min to 7.8 Max	"8"
From 7.8 min to 8.8 Max	"9"
From 8.8 min to 9.8 Max	"10"
From 10.3 min to 11.3 Max	"11.5"

*CABLE DIAMETER UNDER THE GLAND. IF THE CABLE HAS A SLEEVE, THE DIAMETER OVER THE SLEEVE SHOULD BE CONSIDERED THE TOLERANCE OF ØD SHOULD BE TAKEN INTO ACCOUNT TO MAKE SURE IT IS ALWAYS WITHIN THE SPECIFIED RANGE

TOLERANCES UNLESS OTHERWISE SPECIFIED			tolerance std	material	-	dr	BONEY THOMAS	11-15-2018	projection	mm	size	A3	scale	3:10	
				mat code	-	eng	BONEY THOMAS	11-15-2018			ecn no	-			
linear	X.	±-	ISO 406	heattreat	-	chr	S.ALOSIUS	11-15-2018			rel level			In Work	
	0.X	±0.3	ISO 1101	plating/finish	-	appr	BIJU K PAUL	11-15-2018			product family			OCTIS	
	0.XX	±0.13	surface	spec ref	model name	10149875-101LF	Amphenol FCI	title			OCTIS PLUG KIT SFP/SFP+	dwg no	10149875	rev	2
	0.XXX	±0.05													
	0.XXXX	±-													
angular	0°	±2°	ISO 1302	model revision	1		cat. no.	-	Product - Customer Drw			sheet 3 of 3			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10149875-102LF](#) [10149875-101LF](#)