






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN-8B0552	2008/09/22	Shin	Add Note
C	LEN-940062	2009/03/17	LiuShuYun	Change 2.50 to 2.5
D	CI90269	2019/02/26	Ruru	Modify Note & Change Logo




Pin Assignments
Front View



Recommended Panel Cut-Out

With Liquid Glue



Note:

- * Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated
- * Housing: Thermoplastic, Black
- * Pin: Copper Alloy, Gold Plated
- * Nut: Thermoplastic, Black
- * Gasket: Rubber, Black

- * Use with waterproof cap or dust cap
Panel Thickness Max: 4.0mm
- * Use without waterproof cap or dust cap
Panel Thickness Max: 5.0mm
- * Gasket and Nut are packed separately in PE bags.

UNIT:mm		TITLE		Amphenol LTW		ITEM NO	DRAWN BY	DATE
TOLERANCE		Standard,Rear Lock 10P M Conn M Pin		安費諾亮泰企業股份有限公司		BU-10RMMS-LC7001	Ruru	2019-02-26
.X	±0.25	SCALE	1:1	SIZE	A4	DWG NO	CHECKED BY	DATE
.XX	±0.1	REV.	D	WC-REV.	A.3	BU-10RMMS-LC7001	Rita	2019-02-26
.XXX	±0.05	SHEET 1 OF 1		QC: Inspection item		CUSTOMER	APPROVED BY	DATE
ANGLES	±1°					ALTW	Max	2019-02-26

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[BU-10RMMS-LC7001](#)