


Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.


SECTION A-A

58,6
[2.306]



PG 9

A



Number of contacts	Standard	3	4	5	5S	6	7	7	8	12	14
Contact arrangement	DIN EN 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a
Contact arrangement	IEC 60130-9 ¹⁾			-			-			-	
Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)	
Rated voltage	UL 1977			250 V						60 V	
Rated impulse withstand voltage ²⁾	IEC 60664-1		1500 V (840 V)		1200 V (500 V)	1500 V (840 V)			1200 V (500 V)		
Pollution degree ²⁾	IEC 60664-1				1 (3 ³⁾)						
Installation category	IEC 60664-1				I						
Insulation group	IEC 60664-1				II, 400 ≤ CTI < 600						
Current rating	IEC 60512-5-2 UL 1977				5A/+40°C/+104°F					3A/+40°C/+104°F	
Insulation resistance	IEC 60512-3-1				>10 ¹⁰ Ohm ⁴⁾						
Contact resistance	IEC 60512-2-1				<5m Ohm						
Climatic category	IEC 60668-1				40 / 100 / 56						
Temperatur range	IEC 60668-1				-40°C...+100°C / -40°F...+212°F						
salt spray resistance	DIN IEC 60068-2-11				720h						
IP degree	IEC 60529				IP 67 / IP 65 (in mated condition)						
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	50N	55N	60N	50N			
Mechanical operation	IEC 60512-9-1				silver ≥500 mating cycles gold ≥1000 mating cycles						
Housing material					brass and / or zinc die cast, nickel plated						
Dielectric material					thermoplastic						
Contacts					silver or gold plated, please order contacts separately acc. to drawing M-N 02 015 00XX X (3-8pol) or M-N 02 010 0157 X U (12-14pol)						
Termination technique					crimp						
Wire gauge					2-6 pol (exclusive 5S): 0,09-1,0mm² / 28-18 AWG 5S, 7, 7S, 8pol: 0,09-0,75mm² / 28-20 AWG					0,09-0,25mm² / 28-24 AWG	
Flamability					UL 94 V0						
locking system	IEC 60130-9 DIN EN 61076-2-106				metal screw coupling; tightening torque 0,7Nm						

¹⁾ Edition 2000-05

²⁾ values in brackets are according to DIN EN 61076-2-106

³⁾ designed acc. pollution degree 2; can be used under pollution degree 3 when the rules of IEC 60644-1 are fulfilled

⁴⁾ under operating conditions >10⁸ Ohm

All technical data have been measured in a laboratory environment and can be different during pratical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties. Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.

Parts according to directive 2002/95/EG (RoHS).

	14 (14-a)	C091 11F014 001 2 U
	12 (12-a)	C091 11F012 001 2 U
	8 (08-a)	C091 11F008 001 2 U
	7 (07-b)	C091 11F107 001 2 U
	7 (07-a)	C091 11F007 001 2 U
	6 (06-a)	C091 11F006 001 2 U
	5 (05-b)	C091 11F105 001 2 U
	5 (05-a)	C091 11F005 001 2 U
	4 (04-a)	C091 11F004 001 2 U
	3 (03-a)	C091 11F003 001 2 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number

Gewicht (errechnet) / Calc WT: g

Prüfmaß / Testdimension

Teileindex
Partindexnumber

2014

Gez.

Gepr.

Checked

Datum/Date

27.06.

Name

Mohrlang

Amphenol-Tuchel
Electronics GmbH

01

2014-00467

27.06.14

IM

Index

Änderung/Description

Datum/Date

Name

Maßstab / Scale: 1:1

A3

CUSTOMER DRAWING

Kabeldose PG9

female receptacle

M

C091 11FXXX 001 2 U

Blatt/Sheet
1
1 Bl.

Ers. f. / Replacement for:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C091 11F012 001 2](#)