



Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.



NOTE 1 CONTACT CO-PLANARITY TO BE MAX 0.15.
2 TOLERANCES TO BE ± 0.1 UNLESS OTHERWISE SPECIFIED.
3 DEVICE DESIGN SHALL CONSIDER THE STACKED HEIGHT TO BE 14.5mm MAX.
(RECOMMENDED STACKED HEIGHT IS 13.7mm MAX.)
4 CONTACT AREA :GOLD PLATING 0.2 μ m min
LEAD AREA :GOLD PLATING 0.03 μ m min
UNDER :NICKEL PLATING 2 μ m min
5 DIP AREA :TIN PLATING 1 μ m min
UNDER :NICKEL PLATING 0.6 μ m min




3	LCP	UL94V-0, Black	7	Pick & Place tape	
2	Phosphor Bronze	4	5	PS	Milky-white
1	Copper Alloy	4	4	Stainless Steel	5
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

UNITS mm		SCALE 2 : 1		COUNT 1	DESCRIPTION OF REVISIONS DIS-E-00004011	DESIGNED MO. SHIMOYAMA	CHECKED TU. TANIGUCHI	DATE 20210120
 HIROSE ELECTRIC CO., LTD.		APPROVED : MN. KENJO	20200407	DRAWING NO. EDC-122485-70-00				
		CHECKED : TU. TANIGUCHI	20200407	PART NO. EX80-100S(70)				
		DESIGNED : KIM JAEHYEON	20200407	CODE NO. CL0232-0592-2-70				
		DRAWN : DS. HIROWATARI	20200407	 1/2				

Sep.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

EX80-100S PACKAGING FIGURE



NOTE 6 QUANTITY PER TRAY TO BE 60 PCS MAX.
ORDERING VOLUME TO BE MADE BY QUANTITY OF CONNECTOR.
7 A TYPE AND B TYPE TRAY PILED UP ONE AFTER ANOTHER.

HRS	DRAWING NO.	EDC-122485-70-00
	PART NO.	EX80-100S(70)
	CODE NO.	CL0232-0592-2-70

2/2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[EX80-100S\(70\)](#)