


Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



D	Number of contacts	Standard	3	4	5	5S	6	7	7	8	12	14
	Contact arrangement	DIN EN 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a
	Contact arrangement	IEC 60130-9 ¹⁾			-			-			-	
	Rated voltage ²⁾	IEC 60664-1	300 V (100 V)	300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		
	Rated voltage	UL 1977			250 V						60 V	
	Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (840 V)	1200 V (500 V)	1500 V (840 V)			1200 V (500 V)				
	Pollution degree ²⁾	IEC 60664-1			1 (3 ³⁾)							
	Installation category	IEC 60664-1			I							
	Insulation group	IEC 60664-1			II, 400 ≤ CTI < 600							
	Current rating	IEC 60512-5-2 UL 1977			5A/+40°C/+104°F					3A/+40°C/+104°F		
	Insulation resistance	IEC 60512-3-1			>10 ¹⁰ Ohm ⁴⁾							
	Contact resistance	IEC 60512-2-1			<5m Ohm							
	Climatic category	IEC 60668-1			40 / 100 / 56							
	Temperatur range	IEC 60668-1			-40°C...+100°C / -40°F...+212°F							
	salt spray resistance	DIN IEC 60068-2-11			720h							
	IP degree	IEC 60529			IP 67 / IP 65 (in mated condition)							
	Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	50N	55N	60N		50N		
	Mechanical operation	IEC 60512-9-1			silver ≥500 mating cycles gold ≥1000 mating cycles							
	Housing material				brass and / or zinc die cast, nickel plated							
	Dielectric material				thermoplastic							
	Contacts				silver or gold plated, please order contacts separately acc. to drawing M-N 01 015 00XX X (3-8pol) or M-N 01 010 0157 X U (12-14pol)							
	Termination technique				crimp							
	Wire gauge				2-6 pol (exclusive 5S): 0,09-1,0mm² / 28-18 AWG 5S, 7, 7S, 8pol: 0,09-0,75mm² / 28-20 AWG					0,09-0,25mm² / 28-24 AWG		
	Flamability				UL 94 V0							
	locking system	IEC 60130-9 DIN EN 61076-2-106			metal screw coupling; tightening torque 0,7Nm							

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ designed acc. pollution degree 2; can be used under pollution degree 3 when the rules of IEC 60644-1 are fulfilled
⁴⁾ under operating conditions >10⁸ Ohm

All technical data have been measured in a laboratory environment and can be different during pratical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties. Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
Parts according to directive 2002/95/EG (RoHS).

	14 (14-a)	C091 11K014 000 2 U
	12 (12-a)	C091 11K012 000 2 U
	8 (08-a)	C091 11K008 000 2 U
	7 (07-b)	C091 11K107 000 2 U
	7 (07-a)	C091 11K007 000 2 U
	6 (06-a)	C091 11K006 000 2 U
	5 (05-b)	C091 11K105 000 2 U
	5 (05-a)	C091 11K005 000 2 U
	4 (04-a)	C091 11K004 000 2 U
	3 (03-a)	C091 11K003 000 2 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number

Gewicht (errechnet) / Calc WT: g		Zul. Abw./Tolerances:		Maßstab / Scale: 1:1		A3	
		Prüfmaß / Testdimension				CUSTOMER DRAWING	
Teileindex		Partindexnumber					
				2014	Datum/Date	Name	
				Gez.	08.08.	Mohrlang	
				Gepr.			
				Checked			
				Amphenol-Tuchel Electronics GmbH		Kabelstecker PG7 male cable connector	
03	2014-00467	08.08.14	IM				
Index	Änderung/Description	Datum/Date	Name			Ers. f. / Replacement for:	
						M C091 11KXXX 000 2 U	
						Blatt/Sheet 1	
						1 Bl.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C091-11K005-000-2](#)