




Copied from this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.


Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

INDUSTRIAL@AMPHENOL
TRUSTED GLOBALLY

Valid for contact arrangement: 05b, 07b, 08a, 12a, 14a
Valid for contact arrangement: 03a, 04a, 05a, 06a, 07a



Panel Cutout



Sealing area must be flat and polished.
Provide suitable sealing for the screws.

D	Number of contacts	Standard	3	4	5	5S	6	7	7	8	12	14
	Contact arrangement	DIN EN 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a
	Contact arrangement	IEC 60130-9 ¹⁾			-			-			-	
	Rated voltage ²⁾	IEC 60664-1	300 V (100 V)	300 V (63 V)	100 V (32 V)	300 V (63 V)	100 V (32 V)				150 V (32 V)	
	Rated voltage	UL 1977			250 V						60 V	
	Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (840 V)	1200 V (500 V)	1500 V (840 V)	1200 V (500 V)						
	Pollution degree ²⁾	IEC 60664-1			1 (3 ³⁾)							
	Installation category	IEC 60664-1			I							
	Insulation group	IEC 60664-1			II, 400 ≤ CTI < 600							
	Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C/+104°F						3A/+40°C/+104°F	
	Insulation resistance	IEC 60512-3-1			>10 ¹⁰ Ohm ⁴⁾							
	Contact resistance	IEC 60512-2-1			<5m Ohm							
	Climatic category	IEC 60668-1			40 / 100 / 56							
	Temperatur range	IEC 60668-1			-40°C...+100°C / -40°F...+212°F							
	salt spray resistance	DIN IEC 60068-2-11			720h							
	IP degree	IEC 60529			IP 69K / IP 67 / IP 65 (in mated condition)							
	Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	50N	55N	60N		50N		
	Mechanical operation	IEC 60512-9-1			silver ≥500 mating cycles gold ≥1000 mating cycles							
	Housing material				brass and / or zinc die cast, nickel plated							
	Dielectric material				thermoplastic							
	Contacts				silver or gold plated, please order contacts separately acc. to drawing M-N 02 015 00XX X (3-8pol) or M-N 02 010 0157 X U (12-14pol)							
	Termination technique				crimp							
	Wire gauge				2-6 pol (exclusive 5S): 0,09-1,0mm ² / 28-18 AWG 5S, 7, 7S, 8pol: 0,09-0,75mm ² / 28-20 AWG					0,09-0,25mm ² / 28-24 AWG		
	Flamability				UL 94 V0							
	locking system	IEC 60130-9 DIN EN 61076-2-106			metal screw coupling; tightening torque 1,0-1,5Nm							

¹⁾ Edition 2000-05
²⁾ values in brackets are according to DIN EN 61076-2-106
³⁾ designed acc. pollution degree 2; can be used under pollution degree 3 when the rules of IEC 60644-1 are fulfilled
⁴⁾ under operating conditions >10⁸ Ohm

All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties. Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
Parts according to directive 2002/95/EG (RoHS).

	14 (14-a)	C091 11T014 000 2 U
	12 (12-a)	C091 11T012 000 2 U
	8 (08-a)	C091 11T008 000 2 U
	7 (07-b)	C091 11T107 000 2 U
	7 (07-a)	C091 11T007 000 2 U
	6 (06-a)	C091 11T006 000 2 U
	5 (05-b)	C091 11T105 000 2 U
	5 (05-a)	C091 11T005 000 2 U
	4 (04-a)	C091 11T004 000 2 U
	3 (03-a)	C091 11T003 000 2 U
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number

Gewicht (errechnet) / Calc WT:		Zul. Abw./Tolerances:		Maßstab / Scale: 2:1		A3	
Prüfmaß / Testdimension		ISO 2768-c		DIN / ISO 13715		CUSTOMER DRAWING	
Teileindex / Partindexnumber:		Gez. 23.04.2020		Drawn MCARLE		female receptacle	
Bagatelle change:		Status Released		Gepr. 30.04.2020		Gerätedose	
		Checked MGRIMM		Amphenol Tuchel Industrial GmbH		M C091 11TXXX 000 2 U	
03 202000001		30.04.2020 MCARLE		Blatt / Sheet 1		1 Bl.	
Index Änderungs / Description		Datum / Date		Name		Ers. f. / Replacement for: M-C091 11TXXX 000 2 U Rev02	

FAI2020-0014-18
NXM-V02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C091 11T004 000 2](#)