

DRAWING FOR REFERENCE: This is subject to change without notice  
08/11/2012

TO
R

1			2			3			4		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		
△					△						
△					△						
△					△						

NOTES

- THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑩ TO BE 0.2 TO 0.3 N·m. LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑩ FROM LOOSENING.
- ROTATION EXAMPLES OF REF. NO. ① AND ⑥ ARE SHOWN.
- THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

10	BRASS	NICKEL PLATING
9	PHOSPHOR BRONZE	NICKEL PLATING
8	BRASS	NICKEL PLATING
7	BRASS	NICKEL PLATING
6	BRASS	NICKEL PLATING
5	BRASS	NICKEL PLATING
2	COPPER ALLOY	SILVER PLATING 2μm min.
1	BRASS	NICKEL PLATING

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
4	DIALYL PHTHALATE	(BLACK) UL94V-0	3	DIALYL PHTHALATE	(BLACK) UL94V-0

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	M. Sato 07.03.30	T. Komatsu 07.04.09	E. Kunita 07.04.10	M. Sato 07.04.11	

DRAWING NO.	PART NO.
EDC4-028098-71	RM15TP-10PH(71)

UNITS	CODE NO.
mm	CL109-0857-0-71

HRS HIROSE ELECTRIC CO., LTD.

1 2 3 4 FORM NO. 228

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM15TP-10PH\(71\)](#)