



- Notes
- 1 The recommended tightening torque of REF.NO. ⑨ : 3 N·m.
LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent REF.NO. ⑨ from loosening.
 - 2 This product to be used with cableclamp, JR16WCC-*(72).
* designate diameter of applicable cable.
 - 3 Rotation example of REF.NO. ① and ⑨ are shown.
 - 4 The cable pull and twisting strength and other characteristics may differ,
depending on the cable structure, please confirm before the use.

5	Polyacetal	(White)			
4	Diallyl phthalate	(Black) UL94V-0	9	Zinc alloy	Chrome plating
3	Diallyl phthalate	(Black) UL94V-0	8	Silicone rubber	(Black)
2	Phosphor bronze	Surface area : Gold plating 0.2μm min. Under plating : Nickel plating 3μm min.	7	Brass	Chrome plating
1	Copper alloy	Chrome plating	6	Silicone rubber	(Red)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED
HIROSE ELECTRIC CO., LTD.		APPROVED : HY. KOBAYASHI	16. 04. 04	DRAWING NO.	EDC-111160-72-00
		CHECKED : HY. KOBAYASHI	16. 04. 04	PART NO.	RM15WTPZA-12P(72)
		DESIGNED : HK. NAMAI	16. 04. 01	CODE NO.	CL109-1738-6-72
		DRAWN : HK. NAMAI	16. 04. 01		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM15WTPZA-12P\(72\)](#)