






- Notes
- 1 The recommended clamp torque of ref. No. ⑦: 3 N·m.
LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent ref. No. ⑦ from loosening.
 - 2 When mounted on chassis, be careful reference No. ⑤ is fitted into the indicates groove any biting.
 - 3 Plating
Surface : Gold 0.2 μm min.
Under plating : Nickel 3 μm min.

4	Diallyl phthalate	(Black) UL94V-0			
3	Diallyl phthalate	(Black) UL94V-0	7	Brass	Nickel plating
2	Copper alloy	3	6	Phosphor bronze	Nickel plating
1	Zinc alloy	Chrome plating	5	Silicone rubber	(Black)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.	APPROVED	: HY. KOBAYASHI	16. 01. 22	DRAWING NO.	EDC-111086-72-00		
	CHECKED	: HY. KOBAYASHI	16. 01. 22	PART NO.	RM15WTRZA-10P(72)		
	DESIGNED	: KN. IKEHARA	16. 01. 22	CODE NO.	CL109-1655-0-72		
	DRAWN	: KN. IKEHARA	16. 01. 22				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM15WTRZA-10P\(72\)](#)