



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES 1 ROTATION EXAMPLES OF REF. NO. ① AND ⑥ ARE SHOWN.
- 2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑨ : 0.2 TO 0.3 N · m. LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑨ FROM LOOSENING.
- 3 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑧ : 0.6 TO 0.7 N · m.
- 4 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑥ : 2 TO 3 N · m.
- 5 CLAMP MOVABLE RANGE OF REF. NO. ⑦ MAX 15, MIN 8.
- 6 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER. PLEASE CONFIRM BEFORE THE USE.

5	BRASS	NICKEL PLATING	10	PHOSPHOR BRONZE	NICKEL PLATING
4	DIALLYL PHTHALATE	(BLACK) UL94V-0	9	BRASS	NICKEL PLATING JIS B 1117 M2.6×0.45×2
3	DIALLYL PHTHALATE	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING JIS B 1101 M3×0.5×12
2	BRASS	SILVER PLATING 4 μm min.	7	BRASS	NICKEL PLATING
1	BRASS	NICKEL PLATING	6	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
APPROVED : TP. KOMATSU 20210524				DRAWING NO. EDC-003428-76-00			
CHECKED : HY. KOBAYASHI 20210521				PART NO. RM21TP-20P(76)			
DESIGNED : TY. SUZUKI 20210521				CODE NO. CL0109-0324-8-76			
DRAWN : KR. SUZUKI 20210519				1/1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM21TP-20P\(76\)](#)