



- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑤ : 1.5N · m.
 - 2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑨ : 0.1~0.15N · m.
 - 3 THE RECOMMENDED CLAMP TORQUE LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ① AND NO. ⑨ FROM LOOSENING.
 - 4 ROTATION EXAMPLES OF REF. NO. ① AND NO. ⑤ ARE SHOWN.
 - 5 HAND CRIMP TOOL REF. NO. ⑩ : SR30-10PM-T (CL150-0054-4)
 - 6 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE, PLEASE CONFIRM BEFORE THE USE.

5	BRASS	NICKEL PLATING	10	BRASS	
4	POLYTETRAFLUOROETHYLENE	(WHITE)	9	STEEL	CHROMATE TREATMENT (TRIVALENT CHROMIUM) JIS B 1117 M2.5×3
3	POLYACETAL	(WHITE)	8	BRASS	CHROME PLATING
2	BRASS	SURFACE PLATING : GOLD PLATING 0.2μm min. UNDER PLATING : NICKEL PLATING 3μm min.	7	BRASS	CHROME PLATING
1	ZINC ALLOY	NICKEL PLATING	6	CHLOROPRENE RUBBER	(BLACK)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		APPROVED : HY. KOBAYASHI 18. 02. 22		DRAWING NO. EDC-007281-31-00			
HIROSE ELECTRIC CO., LTD.		CHECKED : HY. KOBAYASHI 18. 02. 22		PART NO. SR30-10PM-6P(31)			
		DESIGNED : TH. KAMEYA 18. 02. 21		CODE NO. CL103-0288-8-31			
		DRAWN : MK. INOUE 18. 02. 06					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[SR30-10PM-6P\(31\)](#)