


- 適用範囲 Coverage
本技術指定書は、GT8E-2022SCF (01) 圧着端子 (CL0758-0033-4-01) の圧着品質基準について規定する。
This Crimp contact specification prescribes Crimp condition of GT8E-2022SCF (CL0758-0033-4-01)
- 適合電線 Conformity electric wire
適合芯線サイズ: AWG#20～#22 Conformity wire size: AWG#20～#22
適合被覆サイズ: $\phi 1.3 \sim \phi 1.5$ Conformity insulation size: $\phi 1.3 \sim \phi 1.5$
- 品質基準 Quality criteria



項 目 Item	寸 法 Dimensions (mm)	備 考 Remarks
被覆位置 Cover location	A	0.1 ~ 0.7
芯線先端位置 Location of tip the code	B	0.1 ~ 0.5 深打ち NG 例は L 部を参照 Ex. Deep crimp (Detail L)
ベルマウス Bell-mouth	C	0.2 ~ 0.4
ベンドアップ Bent-up	D	3° 以内 3° max
ベンドダウン Bent-down	E	3° 以内 3° max
ツイスト Twist	F	± 3° 以内 ± 3° max
ローリング Rolling	G	± 5° 以内 ± 5° max
ランス高さ Lance height	H	0.24 ~ 0.37 0.24 ~ 0.37
カットオフタブ Cut off tab	I	0.2 以下 0.2 max
ストリップ長 Strip length	J	2.0 ~ 2.5
圧着バリ高さ Height of metal cut-out	K	0.3 以下 0.3 max

注 1. クリンプハイトは圧着条件表を参照のこと

Note 1. Refer to a crimp condition list for the crimp height

△	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
0	0				
名 称 TITLE			HRS HIROSE ELECTRIC CO., LTD.		
GT8E-2022SCF (01) CRIMP QUALITY STANDARD			APPROVED	AR. SHIRAI	20190320
			CHECKED	HS. OZAWA	20190319
			DESIGNED	DONGCHAN KIM	20190319
			WRITTEN	DONGCHAN KIM	20190319
技 術 指 定 書 TECHICAL SPECIFICATION			ETAD-T0822-00		△ 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[GT8E-2022SCF\(01\)](#)