

DRAWING F
08/11/2012



SAFETY STANDARD			UL		CSA		TÜV	
OPERATING TEMPERATURE RANGE			-10~+60℃					
RATED VOLTAGE	No. 1, 8, 9, 16		AC120V	AC250V	AC125V	AC250V	AC250V, DC300V	
	OTHERS						AC125V, DC150V	
CURRENT RATING	AWG # 14		10A	3A	10A	3A	10A	
	AWG # 16				8A			
	AWG # 18		3A	1A	3A	1A	5A	
	AWG # 20						2.5A	
	AWG # 22						1A	
	AWG # 24	No. 1, 8, 9, 16	2A	1A	2A	1A		
		OTHERS		1A	0.5A	1A		
	AWG # 26							
AWG # 28								

APPLICABLE CONTACT	AWG NO.
QR/P1-PC1A-※11	AWG #18~24
QR/P1-PC1B-※21	AWG #14~16
QR/P1-PC2A-※11	AWG #24~28
QR/P1-PC2B-※21	AWG #20~24

```

*: 1 INDICATED LOOSE CONTACT
   2 INDICATED CHAIN CONTACT

```

NOTES

- ① THE TOLERANCE FOR EACH TERMINAL HOLE IS ± 0.1 .
- ② OPERATING TEMPERATURE RANGE, RATED VOLTAGE, CURRENT RATING ARE PER TABLE 1.
- ③ APPLICABLE CONTACTS FOR THIS CONNECTOR ARE PER TABLE 2.
4. DIRECTIONS FOR USE
 - (1) PLEASE DON'T USE FOR THE PURPOSE OF INTERRUPTING THE CURRENT.
 - (2) PLEASE USE THIS CONNECTOR IN ENCLOSURE



HRS HIROSE
ELECTRIC
CO., LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[QR/P1-16P-C\(51\)](#)