







REV	DOCUMENT	CHANGED BY	CHECK
1	207447	JLH 14FEB03	SAV



NOTES

- 1 - EXPLOSION PROOF - UNDERWRITERS LAB INC LISTING FOR HAZARDOUS LOCATIONS CLASS I, GROUPS C AND D; CLASS 2 GROUPS E, F AND G
- 2 - EUROPEAN HAZARDOUS LOCATIONS DESIGNATION: EExd IIC T6 CATEGORY II 2 GD
- 3 - ALUMINUM ENCLOSURE FINISHED WITH BLUE AND BLACK EPOXY PAINT
- 4 - 6-32 UNC X (7.92) PAN HEAD TERMINAL SCREW AND LOCKWASHER (SEMS TERMI-LOX) (3 PER BASIC)
- 5 - CAMS MAY BE REPOSITIONED IN 7°20' INCREMENTS
- 6 - 2 BASICS; EACH OPERATES CLOCKWISE AND COUNTER CLOCKWISE
- 7 - FOR USE IN TEMPERATURES UP TO 85°C
- 8 - SEE 7CX CHARTS 1 AND 2 (1 DRAWING) FOR LEVER ACTUATORS
- 9 - WEIGHT: 2.49 LB (1.13 Kg) APPROX
- 10 - UNIT PROVIDES NO SHAFT RESTORING FORCE. THE ACTUATING DEVICE MUST CONTROL MOVEMENT OF SHAFT

CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:		DRAWN		JLH		14FEB03		Honeywell			
OPERATING TORQUE----- 0.37 LB FT (0.50 Nm) MAX		CONTACT ARRANGEMENT		<input checked="" type="checkbox"/> US (inch) CUSTOMARY <input type="checkbox"/> SI (mm) METRIC		CHECK		SAV		14FEB03					
PRETRAVEL----- 15° MAX		S P D T (EACH BASIC)		NO PLACE X ±.040 ±1		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		TITLE							
DIFFERENTIAL TRAVEL----- 10° MAX		L96		ONE PLACE .X ±.030 ±0.4											
OVERTRAVEL-----90° MIN		15A 125, 250 OR 480 VAC		TWO PLACE .XX ±.015 ±0.15											
		1/8HP 125 VAC, 1/4HP 250 VAC		THREE PLACE .XXX ±.005 ±											
		1/2A 125 VDC, 1/4A 250 VDC		ANGLES ±		RAW MATERIAL-COMMERCIAL STANDARD		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED							
		   		THIRD ANGLE PROJECTION		3D PTC		ASME Y14.5M-1994		SCALE FULL		WEIGHT 9		SHEET 1 OF 1	
															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[11CX12E](#)