



Copying of this document and giving it to others and the use or communication of the contents thereof, are forbidden without express authority. Offenders are liable to the payment of damages. All rights are reserved in the event of the grant of a patent or the registration of the utility model or design.

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadensersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.



*for 12, 14 and 19 pol = 7,2

Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19
Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a
Contact arrangement	IEC 60130-9 ⁿ	yes		no	yes		no	yes		no			
Rated voltage ²⁾	IEC 60664-1	300 V (100 V)		300 V (63 V)	100 V (32 V)	300 V (63 V)		100 V (32 V)		150 V (32 V)		60 V (32 V)	
Rated voltage	UL 1977	250V								60V			
Rated impulse withstand voltage ²⁾	IEC 60664-1	1500 V (1500 V)			1200 V (800 V)	1500 V (1500 V)		1200 V (800 V)					
Pollution degree ²⁾	IEC 60664-1	1 (3 ³⁾)											
Installation category	IEC 60664-1	I											
Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600											
Current rating	IEC 60512-5-2 UL 1977	10A/+40°C		7A/+40°C						3A/+40°C			
Insulation resistance	IEC 60512-3-1	>10 ¹⁰ Ohm ⁴⁾											
Contact resistance	IEC 60512-2-1	<5mOhm											
Climatic category	IEC 60668-1	40 / 100 / 56											
Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F											
Salt spray resistance	DIN IEC 60068-2-11, test Ka	720h											
IP degree	IEC 60529	IP 69K / IP 67 / IP 65 (in mated condition)											
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N
mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles											
housing material		brass and / or zinc die cast, nickel plated											
dielectric material		thermoplastic											
sealing material		Chloroprene											
contacts		silver or gold plated											
termination technique		solder											
wire gauge		≤0,5mm² / 20 AWG								≤0,35mm² / 22 AWG			
flamability		UL 94 V0											
locking system	IEC 60130-9 DIN EN 61076-2-106	metal screw coupling; tightening torque 0,7 - 1,5 Nm											

ⁿ Edition 2000-05
ⁿ values in brackets are according to DIN EN 61076-2-106
ⁿ designed acc. pollution degree 2, can be used under pollution degree 3 when the rules of IEC 60644-1 are fulfilled
⁴⁾ under operating conditions >10⁸ Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.
Remark for gold plated contacts:
In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding, particularly the information does not constitute or provide any legal guaranties ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

	19 (19-a)	Ag	C091 31W019 100 2 U	F
		Au	C091 31W019 200 2 U	
	14 (14-b)	Ag	C091 31W114 100 2 U	
		Au	C091 31W114 200 2 U	
	14 (14-a)	Ag	C091 31W014 100 2 U	E
		Au	C091 31W014 200 2 U	
	12 (12-a)	Ag	C091 31W012 100 2 U	
		Au	C091 31W012 200 2 U	
	8 (08-a)	Ag	C091 31W008 100 2 U	D
		Au	C091 31W008 200 2 U	
	7 (07-b)	Ag	C091 31W107 100 2 U	
		Au	C091 31W107 200 2 U	
	7 (07-a)	Ag	C091 31W007 100 2 U	D
		Au	C091 31W007 200 2 U	
	6 (6-a)	Ag	C091 31W006 100 2 U	
		Au	C091 31W006 200 2 U	
	5 (05-b)	Ag	C091 31W105 100 2 U	C
		Au	C091 31W105 200 2 U	
	5 (05-a)	Ag	C091 31W005 100 2 U	
		Au	C091 31W005 200 2 U	
	4 (04-a)	Ag	C091 31W004 100 2 U	B
		Au	C091 31W004 200 2 U	
	3 (03-a)	Ag	C091 31W003 100 2 U	
		Au	C091 31W003 200 2 U	
Contact arrangement View on mating side	Number of contacts (Contact arrangement acc DIN EN 61076-2-106)	contact plating	Part number	

Gewicht (errechnet) / Calc WT: 14,905 g	Zul. Abw./Tolerances:	Maßstab / Scale: 2:1	A3	
Prüfmaß / Testdimension	ISO 2768-c	CUSTOMER DRAWING		
Teileindex / Partindexnumber:				
Bagatelle change: 23.02.2021 MCARLE				
	Gez. 10.06.2020	Male receptacle front mounting		
	Drawn MCARLE			
	Status Released			
	Gepr. 11.01.2021	Amphenol Tuchel Industrial GmbH		
	Checked MBERTSCH			
01 202000083	26.10.2020 MCARLE	M C091 31WXXX X00 2 U	Blatt/Sheet 1	1 Bl.
Index	Änderung/Description	Datum/Date	Name	Ers. f. / Replacement for:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C091-31W008-200-2](#)