



MICRO SWITCH
FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91928

**SWITCH - TOGGLE
FLUSH KEY**

CATALOG LISTING
4TP1 SERIES
CHART 1

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CATALOG LISTING	CIRCUIT MADE WITH BUTTON DEPRESSED ON		
	LUG SIDE (1-2, 4-5, 7-8, 10-11)	CENTER (1-2, 4-5, 7-8, 10-11)	OPPOSITE LUG (2-3, 5-6, 8-9, 11-12)
4TP1-1	ON	OFF	ON
Ⓢ	OFF	NONE	ON
4TP1-3	ON	NONE	ON
4TP1-2I	NONE	OFF	ON
Ⓢ	NONE	ON	ON
4TP1-4	MOM OFF	NONE	ON
4TP1-5	MOM ON	OFF	ON
4TP1-6	MOM ON	NONE	OFF
4TP1-7	MOM ON	OFF	MOM ON
4TP1-8	MOM ON	NONE	ON
4TP1-5I	NONE	ON	MOM ON
4TP1-6I	MOM ON	OFF	NONE

ELECTRICAL DATA	
15A-125, 250 OR 277 VAC Ⓢ CE 1/2HP-125VAC; 1HP-250, 277VAC 5A-125VAC "L" CODE L191	
10A-125, 250, 277 VAC Ⓢ CE 1/4HP-125VAC; 1/2HP-250, 277 VAC 3A-125VAC "L" CODE L192	

- NOTES
- 1 - CIRCUIT DESIGNATION AND MICRO SWITCH CATALOG LISTING MARKED ON SIDE OF SWITCH
 - 2 - THESE SWITCHES WILL WITHSTAND TEMPERATURE OF 160°F
 - 3 - APPLIES ONLY TO "ON" AND "MOMENTARY ON" POSITIONS
 - 4 - SCREWS FURNISHED UNASSEMBLED

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE:

	DIM.	TOL.	DIM.	TOL.
	mm	mm/in	in	mm/in
NO PLACES	X	1/64	X	0.075
ONE PLACE	X, X	0.01/0.10	X, X	0.001/0.11
TWO PLACES	X, X	0.10/0.005	X, X	0.002/0.005
THREE PLACES	X, X	0.001/0.0005	X, X	0.0001/0.0005

DESIGN UNITS ☐ METRIC ☒ US CUSTOMARY

WEIGHT .22 LB EST

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Honeywell:

[4TP1-1](#) [4TP12-1](#) [4TP1-3](#) [4TP1-7](#)