

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH — BASIC

CATALOG LISTING

V7-1B17D8-122



CW-B2036

CATALOG LISTING
V7-1B17D8-122
PAGE 1 OF 1
RELEASE NO. PR-23344
REPLACES
ISSUE
2

REVISIONS

APR 23 1998
DCS
12 FEB 98


DDM/CAD
DRAWN
DCS
30 JAN 98
CHECK
DCS
12 FEB 98
CHECK





ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE— — —43 GRAMS MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT	
RELEASE FORCE— — —4 GRAMS MIN	L156 11A 1/3HP 125, <u>250</u> OR 277 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L"		
DIFFERENTIAL TRAVEL— — —.053 MAX			
OVERTRAVEL— — — — —.118 MIN			
RELEASE TRAVEL— — — — —.032 MIN			





Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1B17D8-122](#)