


Dimension



DIM A	N×5.08
DIM B	(N-1)×5.08

N=Number of contacts

Poles	Tolerance
4P-8P	±0.15
9P-14P	±0.25
15P-20P	±0.35
21P-24P	±0.40



N=Number of contacts



SIGN	DATE	DESCRIPTION	APPROVER
△	10/26/09	Wire guard solder pin is Changed from Brass to Copper	Aaron
△	11/09/10	Add is " VDE "	Aaron

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item 1 Terminal housing:Thermoplastic (UL 94V-0)
- Item 2 Clamp: Brass Ni plated
- △ Item 3 Wire guard solder pin:Copper Tin plated
- Item 4 Terminal screw: Steel Zinc plating"-slot type

- △ Electrical cULus VDE
  - Voltage rating: 300VAC 450V
  - Current rating: 20A 24A
  - Wire range : 0.2-2.5mm<sup>2</sup>
  - Solid wire(AWG): 12-30
  - Stranded wire(AWG): 12-30
  - Torque(Lb-In): 3.5 0.5 N.m
  - Screw: M3
  - Wire strip length: 6-7mm
  - Withstanding Voltage: 1.6KV 2.5KV
  - Operating temperature: -40°C to +115°C
  - Soldering temperature: 250°C±10°C/5 Sec
  - Safety Approval:

VJ xx 21 x 3 xxxx G

No. of poles		RoHS Pb<40,000ppm
04 4 CONTACTS	0 Black (RAL9005)	0000:"@ "Logo (Standard )
05 5 CONTACTS	2 Red (RAL3001/D)	000A:"ANYTEK"Logo
...	3 Orange(RAL2011/P)	Any special item by
24 24 CONTACTS	4 Yellow(RAL1018/A)	customer request,
	5 Green(RAL6018/T)	please contact sales
	6 Blue (RAL5015/A)	department.
	8 Grey(RAL7035/D)	

**ANYTEK**

**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VJ-5.08 Series 4P-24P Vertical solid block ( 90D wire inlet )				
PART NO.	VJxx21x3xxxxG			DWG NO.	8VJ0115
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Aaron 2010.11.09	Aaron 2009.10.26		Tolerance X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
					UNIT: mm SCALE: NONE SHEET: 01/01 REV: D

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Amphenol:

[VJ0421530000G](#) [VJ0521530000G](#) [VJ0621530000G](#) [VJ0721530000G](#) [VJ0821530000G](#) [VJ0921530000G](#)  
[VJ1021530000G](#) [VJ1121530000G](#) [VJ1221530000G](#) [VJ1321530000G](#) [VJ1421530000G](#) [VJ1521530000G](#)  
[VJ1621530000G](#) [VJ1721530000G](#) [VJ1821530000G](#) [VJ1921530000G](#) [VJ2021530000G](#) [VJ2121530000G](#)  
[VJ2221530000G](#) [VJ2321530000G](#) [VJ2421530000G](#)