

MICRO SWITCH

FREEDPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RW8255-A2-S

BZ-2RW8255-A2-S

PAGE 1 OF 1

REPLACES

RELEASE NO. PR-6725

DRAWING
NUMBER

7

ISSUE

CHECK

REVISIONS

A	CO	39621
T	M	M
16	DEC	77
B	CO	67209
J	A	P
3	MAY	90
C	CO-	73287-J
J	A	L
22	NOV	93
D	CO-	75204B
K	D	R
1	FEB	94
E	CO-	77588
K	D	R
29	MAR	94
F	CO	93346
DLT		
11	SEP	98

CHECK

17 OCT 77

SLH

77 CHECK


12 OCT 77

12 OCT 77

FORMTEK

FO-52848-A

1 DRAWN




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — 3 1/2 OZ MAX
RELEASE FORCE — — 3/4 OZ MIN
DIFFERENTIAL TRAVEL — .004 — .040
OVERTRAVEL — — — .156 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L98 15A 125, 250 OR 480 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

L288
L299
L306
CE D RJ

16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DIMENSION UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.01/06
ONE PLACE	X,X	0.4/.016	X,X	0.38/.016
TWO PLACES	X,X,X	0.18/.008	X,X,X	0.13/.008
THREE PLACES				
ANGLES				

DESIGN UNITS ☒ METRIC ☐ US CUSTOMARY

WEIGHT .079 LB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RW8255-A2-S](#)