

# MICRO SWITCH

FREEDPORT ILLINOIS, U.S.A  
A DIVISION OF HONEYWELL  
FED. MFG. CODE 91929

## SWITCH-BASIC

CATALOG LISTING

BZ-2RW855-A2-S

BZ-2RW855-A2-S

PAGE 1 OF 1

M

DRAWING  
NUMBER

6

ISSUE

REPLACES

RELEASE NO. PR-6725

CHECK

REVISIONS

A	CO	39621
T	M	16 DEC 77
B	CO	67209
J	A	P
3	MAY	90
C	CO	73287-J
J	A	L
22	NOV	93
D	CO	77588
K	D	R
29	MAR	94
E	CO	93346
D	L	T
14	SEP	98

CHECK

17 OCT 77

17 OCT 77


12 OCT 77

FORMTEK

FO-52848-A

DRAWN

12 OCT 77




### NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- 2 SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



### CHARACTERISTICS

OPERATING FORCE --- 2 1/2 OZ MAX  
RELEASE FORCE --- 1/2 OZ MIN  
DIFFERENTIAL TRAVEL --- .007-.050  
OVERTRAVEL --- .219 MIN

### ELECTRICAL DATA

CONTACT ARRANGEMENT  
S P D T

L96

15A 125, 250 OR 480 VAC  
1/8 HP 125 VAC, 1/4 HP 250 VAC  
1/2A 125 VDC, 1/4A 250 VDC

L288  
L299  
L306

CE D A E

16A 250V ~ T85 5E4

### SCALE FULL

DO NOT SCALE PRINT

TOLERANCES  
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DNM. mm	TOL. mm/in	DNM. in	TOL. mm/in
NO PLACES	X	17.04	X	0.07/03
ONE PLACE	X,X	0.47/018	X,X	0.387/015
TWO PLACES	X,X,X	0.157/006	X,X,X	0.137/005
THREE PLACES	X,X,X,X		X,X,X,X	
ANGLES				

DESIGN UNITS ☐ SI METRIC

US CUSTOMARY ☒

WEIGHT, 076 LB

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RW855-A2-S](#)