

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING
BA-2RV-A4

ABN7506

BA-2RV-A4

PAGE 1 OF 1

M

DRAWING
NUMBER

6

ISSUE

REPLACES

RELEASE NO. PR-6975

CHECK

REVISIONS

A	CO	51554	TSK	19 JULY 82
B	CO	73287-6	JAL	20 OCT 93
C	CO	77588	KDR	29 MAR 94
D	CO	93346	DLT	26 AUG 98
E	CO	0018387	TSG	18 JAN 06

RJ

CHECK

78

14

CEB

CHECK

78

13

FEB

78

FORMTEK

FO-52848-A

DRAWN


3X 8-32 UNC (.219) BINDING
HEAD COMBINATION TERMINAL
SCREW AND CUPWASHER

NOTE

MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 2 1/2 OZ MAX
RELEASE FORCE — — — — — 1/2 OZ MIN
PRETRAVEL — — — — — .625 MAX
DIFFERENTIAL TRAVEL — — — .109 MAX
OVERTRAVEL — — — — — .078 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

CODE L23

20A-125, 250 OR 480 VAC; 10A-125 VAC "L"
1HP-125 VAC; 2HP-250 VAC
1/2A-125 VDC; 1/4A-250 VDC

L288
L308
L315



20(3)A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED TOLERANCES ARE X

NO PLACES	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
ONE PLACE	X	1/64	X	0.015
TWO PLACES	X, XX	0.001	X, XX	0.0005
THREE PLACES	X, XX, XXX	0.0005	X, XX, XXX	0.0002

DESIGN UNITS ☐ SI METRIC ☒ US CUSTOMARY

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BA-2RV-A4](#)