










- * Waterproof Rate: IP68
- * Screw Nut: Nylon, Gray
- * Clamp Ring: Nylon, Gray
- * Sealing Nut: Nylon, Gray
- * Gasket: EPDM, Black
- * Seals: EPDM, Black
- * Cable Range: $\varnothing 6.0 \sim \varnothing 10.0 \text{mm}$
- * For Panel Thickness: 7.5mm max
- * Spanner Size:
 - Body: 22.0mm
 - Sealing Nut: 22.9mm
 - Screw Nut: 22.0mm



UNIT : mm				TITLE PG9 Gland, Knock Hole		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO CSG-09G005		DRAWN BY Ruru		DATE 2015-05-12					
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±		SCALE 1 : 1						SIZE A4		SHEET 1 OF 1		DWG NO CSG-09G005		CHECKED BY Rita		DATE 2015-05-12	
		REV. B						WC-REV. A.1		QC: Inspection item		CUSTOMER ALTW		APPROVED BY Lion		DATE 2015-05-12	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[CSG-09G005](#)